

Series variation



Balancer unit BBS Series

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MecHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending

Variation	Model No.	Bore size (mm)	Stroke (mm)	
Auto pressure adjustment	BBS-A	ø50/ø63 ø80/ø100	100/200/300/400/500/600/700/800/900/ 1000/1100/1200/1300/1400/1500	
Fixed pressure adjustment control box separate	BBS-O	ø50/ø63 ø80/ø100	100/200/300/400/500/600/700/800/900/ 1000/1100/1200/1300/1400/1500	
Fixed pressure adjustment control box integrated	BBS-OB	ø50/ø63 ø80/ø100	100/200/300/400/500/600/700/800/900/ 1000/1100/1200/1300/1400/1500	

●: Standard ◎: Option ■: Not available

	Max. stroke	Min. stroke	Mounting					Accessory		Page
			Basic	Eye bracket	Clevis bracket	Rod side flange	Head side flange	Rod eye	Rod clevis	
	(mm)	(mm)	00	CA	CB	FA	FB	I	Y	
	1500	100	●	●	■	●	●	●	●	1258
			●	■	●	●	●	●	●	
	1500	100	●	●	■	●	●	●	●	1270
			●	■	●	●	●	●	●	
	1500	300	●	●	■	●	●	●	●	1270
			●	■	●	●	●	●	●	

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending