


Quick exhaust valve inline type

QEL Series

● Piping bore size: $\phi 4/\phi 6$



Pneumatic, Vacuum and Auxiliary Components
Catalog No. CB-024SA



Features

- Compact/space saving inline
With $\phi 4/\phi 6$ push-in fitting
Atmosphere release type and type with exhaust port fitting are available
- Ozone-resistant materials as standard
Ozone-resistant materials are used as standard for to prevent degradation of the valving element
- Ecological products
All substances which adversely affect the global environment have been eliminated from the materials
RoHS Directive compliant products

Specifications

Model No.	QEL-H44	QEL-H66
Working fluid	Compressed air	
Max. working pressure MPa	0.7	
Min. working pressure MPa	0.1	
Min. working pressure MPa	0.05	
Proof pressure (normal temperature) MPa	1.35	
Operating ambient temperature range °C	5 to 60 (no freezing)	
Port size	IN, OUT	$\phi 4$
	EXH	$\phi 6$
Product weight g	5.2	7.6
Mounting orientation	Unrestricted	
Effective cross-sectional area	IN→OUT mm ²	1.8
	OUT→EXH mm ²	1.8
	4	4

Compatibility table by variation

	QEL
Port size	$\phi 4, \phi 6$
P4	▲

●: Applicable models ○: Semi-applicable models ▲: Contact CKD for details. □: Not applicable
*1: Applicable only for type with exhaust port fitting.

How to order

QEL - H44 - P4

Model No.

● A Compatible tube O.D.

Code	Content
A	Compatible tube O.D
H44	$\phi 4$
H66	$\phi 6$

● B Option

Code	Content
B	Option
Blank	Type with exhaust port fitting

Note: It is a made-to-order product.
Contact CKD Sales for details.

Applications

