



Pneumatic, Vacuum and Auxiliary Components
Catalog No. CB-024SA

Miniature fitting FTS4/FPL Series

● Port size: M3 to 1/8



P4
Series

Specifications

Item	F
Working fluid	Compressed air
Max. working pressure MPa	0.7 or less
Ambient/fluid temperatures °C	-5 to 60 (no freezing)
Tube used	Soft nylon tube (model No. FH-3224, F-1504, F-1506) Urethane tube (model No. U-9504, U-9506) Note

Note: Use urethane tubes within the range of 0 to 60°C.

Refer to "Pneumatic, Vacuum and Auxiliary Components" (catalog No. CB-024SA) for tube dimensions and working pressure.

Compatibility table by variation

	FTS4	FPL
Port size	M3	M5
P4	▲	▲

● : Applicable models ○ : Semi-applicable models

▲ : Contact CKD for details. □ : Not applicable

Note : M3 gasket dimensions are different from the standard dimensions.

How to order

• Straight, compatible tube O.D. $\varnothing 3.2$, $\varnothing 4$, port size M3

FTS4 – **M3** – **P4**

• Plug, port size M5

FPL – **M5** – **P4**

*1: Refer to "Pneumatic, Vacuum and Auxiliary Components" (catalog No. CB-024SA) for details on model combinations.

*2: Sales unit is 10 pcs./1 bag. Sales unit of each model is 10/1 bagit will be .

*3: Made-to-order product. Contact CKD Sales for details.

Pneumatic cylinders
Hand/ Chuck
Related products
Cylinder Switch
Pneumatic actuator
Vacuum components
Pneumatic valves
Clean air components
Speed controller
Pneumatic auxiliary components
Fitting
Auxiliary valve
Silencer
Tube
Gas generator
Fluid control components
Electric actuator
Motor specification
Motorless specifications