

Introduction of made-to-order products

		Page
Flow sensor for air unit	CXU30-FSM2	Ending Page 19
Flow sensor for clean air unit	CAU30-FSM2	Ending Page 19
Block needle valve for air unit	CXU30	Ending Page 19
Drain outlet custom made	W/F/M3000 / 4000	Ending Page 19
Drain outlet barbed nipple	B7019-2C	Ending Page 19
Water filter	A1019	Ending Page 19
Pressure gauge with proximity switch	G59D	Ending Page 19
With set pressure upper limit stopper	RPE1000	Ending Page 20
Knob lock mechanism	R3000/4000	Ending Page 20
Residual pressure exhaust valve	PBC	Ending Page 20
White Vaseline	W/F/R*000,QEV2,SHV2	Ending Page 21
Fluorine	W/F/R*000	Ending Page 21
Vaseline coating	CHV2,GW	Ending Page 21

Made-to-order products

Available as made-to-order products. Contact CKD for details.

CXU30-FSM2 Flow sensor for air unit

- Air unit and module can be connected
- Flow rate range 500, 1000 l/min (ANR)

CAU30-FSM2 Flow sensor for clean air unit

- Clean air unit and module can be connected
- Flow rate range 500, 1000 l/min (ANR)

CXU30 Block needle valve for air unit

- Air unit and module can be connected
- Flow rate adjustment needle valve

W/F/M3000 / 4000 Drain outlet custom made

- Drain outlet bore size: Rc1/8, Rc1/4
- Port size: Rc1/4, Rc3/8, Rc1/2

B7019-2C Drain outlet barbed nipple

- With piston drain (D) for drain piping
- Recommended tube: 3/16 (inch size inner diameter: ø2.99)

A1019 Vacuum filter

- Fluid: general industrial clear water
- Filtration: 100 µm
- Port size: Rc1/4



G59D Pressure gauge with proximity switch

- Proximity output with no risk of contact failure
- PNP transistor/open collector
- Outer diameter: ø52.5, Port size: R1/4, full scale: 1.0 MPa
- Switch setting range: 0.1 to 0.8 MPa



Made-to-order products

Made-to-order products (safety)

Available as made-to-order products. Contact CKD for details.

RPE1000 With set pressure upper limit stopper

- Set upper pressure limit mechanism with stopper
- Port size: Rc1/4



R3000/4000 Knob lock mechanism

- Knob lock mechanism with special screw
- Port size: Rc1/4, Rc3/8, Rc1/2



PBC Residual pressure exhaust valve

- Discharges residual pressure between drive valve and cylinder
- Port size: Rc1/4
- Basic and 3-way valve integrated are available

Made-to-order products (grease custom made)

Available as made-to-order products. Contact CKD for details.

W/F/R*000 White Vaseline

- Changes grease in fluid passage into white Vaseline
- Port size: Rc1/8, Rc1/4, Rc3/8, Rc1/2, Rc3/4, Rc1



W/F/R*000 Fluorine

- Changes grease in fluid passage into fluorine grease
- Port size: Rc1/8, Rc1/4, Rc3/8, Rc1/2, Rc3/4, Rc1



QEV2 White Vaseline

- Changes grease in fluid passage into white Vaseline
- Port size: Rc1/8 to Rc1



SHV2 White Vaseline

- Changes grease in fluid passage into white Vaseline
- Port size: Rc1/8 to Rc1

