

M4G Individual wiring

M4G^{D₂E₃} 1 Manifold specifications sheet

Date issued / /

Company

Contact

Order No.

● Contact

● Quantity/set(s)

● Delivery date /

Slip No.

Order No.

● Manifold model No.

M G^{D₂} 0EJ - - - - -

Solenoid valves Solenoid position Port size Electrical connections Other options Mount type Station No. Voltage

Solenoid valve model No.		Fitting CX		Valve installation position																								Quantity	
		A	B	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24		
4G	9EJ																												
4G	9EJ																												
4G	9EJ																												
4G	9EJ																												
4G	9EJ																												
3G	9EJ																												
3G	9EJ																												
Masking plate 4G R-MP-																													
Air supply spacer 4G R-P-																													
In-stop valve spacer 4G R-IS																													
Exhaust spacer 4G R-R-																													
Mounting rail L ₂ = * Write an integer multiple of 12.5.	Included part	Blanking plug																For M/G ₂ 1/0EJ											
		GWP 4-B		GWP 6-B		GWP 8-B		GWP 10-B		Push-in fitting tube remover ☐ required (check)																			
		Threaded plug																											
		4G1R-M5P		4G2R-06P		4G3R-08P																							
		Silencer																											
		SLW-6S		SLW-6A		SLW-8S		SLW-8A		SLW-10S		SLW-10A																	

