

List of attachments

Basic

Motor mounting bolt (common motor mounting direction)

Model No.	Mounted motor specification	Motor capacity	Size	Quantity
ETS-05	M	100 W	M4	2
	Y		M4	2
	P		M3	4
	F		M4	2
ETS-06	M	50 W/100 W	M4	2
	Y		M4	2
	P		M3	4
	F		M4	2
ETS-10 ETS-12	M	100 W/200 W	M4/M5	2/4
	Y		M4/M5	2/4
	P		M3/M4	4
	F		M4/M5	2/4
ETS-13	M	100 W/200 W/400 W	M4/M5/M5	2/4/4
	Y		M4/M5/M5	2/4/4
	P		M3/M4/M4	4
	F		M4/M5/M5	2/4/4
ETS-14	M	200 W/400 W	M5	4
	Y		M5	4
	P		M4	4
	F		M5	4
ETS-17	M	400 W	M5	4
	Y		M5	4
	P		M4	4
	F		M5	4
	M	750 W	M6	4
ETS-22	Y		M6	4
	P		M5	4
	F		M6	4

By motor mounting direction

Model No.	Attachment name	Quantity
E (external direct mounting) B (built-in)	Coupling (assembled at shipment)	1
R (right-side mounting) L (left-side mounting)	Timing belt	1
D (bottom mounting)	Pulley	1

When origin/limit sensor is selected *1

Sensor mounting direction	Shipping format	Quantity
Inside sensor	Fixed position assembled at shipment	3 *2
Outside sensor	Included at shipment *3	

*1 Shipping format varies according to whether origin sensor and limit sensor are assembled inside or outside.

*2 When "None" is selected for origin sensor or limit sensor, the other sensor is also "None".

*3 Sensor mounting screws are also included.

Maintenance parts

● Maintenance parts set

Model No.	Compatibility	Components			
		(1)	(2)	(3)	(4)
		Timing belt 	Pulley 	Sensor dog 	Photoelectric bracket 
ETS-08JP002-0001	ETS-05	○ (1 pc)	○ (1 pc)	○ (1 pc)	-
ETS-08JP002-0002	ETS-06	○ (2 pcs)	○ (1 pc)	○ (1 pc)	-
ETS-08JP002-0003	ETS-10	○ (3 pcs)	○ (2 pcs)	○ (1 pc)	○ (4 pcs)
ETS-08JP002-0004	ETS-12	○ (2 pcs)	○ (2 pcs)	○ (1 pc)	○ (4 pcs)
ETS-08JP002-0005	ETS-13, 14	○ (2 pcs)	○ (3 pcs)	○ (1 pc)	-
ETS-08JP002-0007	ETS-17	○ (4 pcs)	○ (2 pcs)	○ (1 pc)	-
ETS-08JP002-0008	ETS-22	○ (3 pcs)	○ (2 pcs)	○ (1 pc)	-

*Contact CKD regarding maintenance parts for metal stopper specifications (ETS-X).

● Maintenance parts (coupling)

Model No. 	Compatibility	Motor capacity	Hole diameter
ETS-22007-000136	ETS-05, 06	100 W	ø8
ETS-22007-000014	ETS-10, 12	100 W	ø8
ETS-22007-000289	ETS-10, 12, 13, 14 (Mounted motor specification: F)	200 W	ø9
ETS-22007-000016	ETS-10, 12, 13, 14 (Mounted motor specification: P)	200 W	ø11
ETS-22007-000017	ETS-10, 12, 13, 14 (Mounted motor specification: M, Y)	200 W/400 W	ø14
ETS-22007-000022	ETS-17 (Mounted motor specification: P)	400 W	ø14
ETS-22007-000358	ETS-17 (Mounted motor specification: F)	750 W	ø14
ETS-22007-000397	ETS-22 (Mounted motor specification: F)	750 W	ø14
ETS-22007-000024	ETS-17 (Mounted motor specification: M, Y)	750 W	ø19
ETS-22007-000029	ETS-22 (Mounted motor specification: M, Y, P)	750 W	ø19

● Maintenance parts (outside mounted sensor)

Basic price model No. 	Compatibility	Part
ETS-22008-000001	All models	Body
ETS-22008-000006		Cable