

Series variation



Rodless cylinder SR*3 Series

SCP*3
CMK2
CMA2
SCM
SCG
SCA2
SCS2
CKV2
CAV2/
COVPIN2
SSD2
SSG
SSD
CAT
MDC2
MVC
SMG
MSD/
MSDG
FC*
STK
SRL3
SRG3
SRM3
SRT3
MRL2
MRG2
SM-25
ShkAbs
FJ
FK
Spd
Contr
Ending

Variation/model No.	Bore size (equiv.)										Page
	ø12	ø16	ø20	ø25	ø32	ø40	ø50	ø63	ø80	ø100	
Basic SRL3 Series 	●	●	●	●	●	●	●	●	●	●	1574
Basic model of space saving											
Resin guide SRL3-G Series 	●	●	●	●	●	●	●	●	●	●	1590
With simple resin guide											
High precision guide (with 1-axis linear guide) SRG3 Series 	●	●	●	●							1650
With high precision guide											
High precision guide (with 2-axis linear guide) SRM3 Series 				●	●	●		●			1676
With high precision guide											
With brake SRT3 Series 	●	●	●	●	●	●	●	●			1706
With brake											
Standard/position locking SRL3-Q Series 	●	●	●	●	●	●	●	●	●	●	1604
Standard/with position locking function											
Resin guide/position locking SRL3-GQ Series 	●	●	●	●	●	●	●	●	●	●	1614
With simple resin guide/position locking function											
High precision guide/position locking (with 2-axis linear guide) SRM3-Q Series 				●	●	●	●	●			1676
High precision guide/with position locking function											