

4GA/B
M4GA/B
MN4GA/B
4GA/B (master)
4GB With sensor
4GD/E
M4GD/E
MN4GD/E
4GA/B4
MN3E MN4E
W4GA/B2
W4GB4
MN3S0 MN4S0
4SA/B0
4KA/B
4KA/B (master)
4F
4F (master)
PV5G GMF
PV5 GMF
PV5S-0
3Q
MV3QR
3MA/B0
3PA/B
P/M/B
NP/NAP NVP
4G*0EJ
4F*0EX
4F*0E
HMV HSV
2QV 3QV
SKH
Silencer
TotAirSys (Total Air)
TotAirSys (Gamma)
Ending

M4F**E Manifold specifications sheet

Date issued / /

Company

Contact

Order No.

● Contact ● Quantity set(s) ● Delivery date /

Slip No. Order No.

If instructions are provided for combinations of solenoid valves, changes of piping ports, etc., with this manifold specifications sheet, units will be delivered with the corresponding items assembled. When using this specifications sheet to place an order, contact CKD about the manifold model, etc.

● Manifold model No.

M4F

B

 0E -

C

 -

D

 P -

E

F

 -

G

 -

H

I

 -

J

3 to 7

 Solenoid position

Port size
(C1/C2)

External wire
pull method

Option

Thermal class

Station No.

Exhaust
method

Installation feet
(For 4F3)

Voltage

Solenoid valve			Installation position										Subtotal	Total
	Model	Bore size	1	2	3	4	5	6	7	8	9	10		
2-position Single	4F													
2-position Double	4F													
3-position all Ports block	4F													
3-position A/B/R Connection	4F													
3-position P/A/B Connection	4F													
Masking plate														