

4GA/B
M4GA/B
MN4GA/B
4GA/B (master)
4GB With sensor
4GD/E
M4GD/E
MN4GD/E
4GA4/B4
MN3E MN4E
W4GA/B2
W4GB4
MN3S0 MN4S0
4SA/B0
4KA/B
4KA/B (master)
4F
4F (master)
PV5G GMF
PV5 GMF
PV5S-0
3Q
MV3QR
3MA/B0
3PA/B
P/M/B
NP/NAP NVP
4G*0EJ
4F*0EX
4F*0E
HMV HSV
2QV 3QV
SKH
Silencer
TotAirSys (Total Air)
TotAirSys (Gamma)
Ending

# M4F\*\*EX      Manifold specifications sheet

Date issued      /      /

Company

Contact

Order No.

● Contact      ● Quantity/set(s)      ● Delivery date /

Slip No.      Orders No.

If instructions are provided for combinations of solenoid valves, changes of piping ports, etc., with this manifold specifications sheet, units will be delivered with the corresponding items assembled. Place to order with this specifications sheet and manifold model No., etc., contact CKD separately.

● Manifold model No.

M4F

3 to 7

0EX-

Port size  
(C1/C2port)

-G

Option

-

Station  
No.

-

Exhaust  
method

-

Installation feet  
(For 4F3)

-

Voltage

-

Explosion-  
proof  
certification  
organ

Solenoid position      Applicable cable  
O.D.      Station  
No.      Installation feet  
(For 4F3)      Voltage      Explosion-  
proof  
certification  
organ

Solenoid valve			Installation position										Subtotal	Total
	Model	Bore size	1	2	3	4	5	6	7	8	9	10		
2-position Single	4F <div></div>													
2-position Double	4F <div></div>													
3-position all Port block	4F <div></div>													
3-position A/B/R Connection	4F <div></div>													
3-position P/A/B Connection	4F <div></div>													
Masking plate														