



Internal structure and parts list



NW4GB410 base side piping

● 2-position single



NW4GZ410 base bottom piping * The solenoid valve is the same as NW4GB410.

● 2-position single



Main parts list

No.	Part name	Material	No.	Part name	Material
1	Cap D3	PA	8	Wiring connector	-
2	Piston assembly	-	9	Body	Aluminum
3	Quick exhaust valve	H-NBR	10	Wiring base	-
4	Pilot valve	-	11	Spool assembly	-
5	Manual override	PBT	12	Drip-proof cover	PBT
6	Pilot valve assembly SD	-	13	Cap S	PA
7	Decorative cover	PBT	14	Valve block	Aluminum



4GA/B
M4GA/B
MN4GA/B
4GA/B (master)
4GB With sensor
4GD/E
M4GD/E
MN4GD/E
4GA4/B4
MN3E MN4E
W4GA/B2
W4GB4
MN3S0 MN4S0
4SA/B0
4KA/B
4KA/B (master)
4F
4F (master)
PV5G GMF
PV5 GMF
PV5S-0
3Q
MV3QR
3MA/B0
3PA/B
P/M/B
NP/NAP NVP
4G*0EJ
4F*0EX
4F*0E
HMV HSV
2QV 3QV
SKH
Silencer
TotAirSys (Total Air)
TotAirSys (Gamma)
Ending

4GA/B
M4GA/B
MN4GA/B
4GA/B (master)
4GB With sensor
4GD/E
M4GD/E
MN4GD/E
4GA/B4
MN3E MN4E
W4GA/B2
W4GB4
MN3S0 MN4S0
4SA/B0
4KA/B
4KA/B (master)
4F
4F (master)
PV5G GMF
PV5 GMF
PV5S-0
3Q
MV3QR
3MA/B0
3PA/B
P/M/B
NP/NAP NVP
4G*0EJ
4F*0EX
4F*0E
HMV HSV
2QV 3QV
SKH
Silencer
TotAirSys (Total Air)
TotAirSys (Gamma)
Ending

Internal structure and parts list



W4GB410 Single unit Base side piping

● 2-position single



W4GZ410 Single unit Base bottom piping

● 2-position single



* The solenoid valve is the same as W4GB410.



Main parts list

No.	Part name	Material	No.	Part name	Material
1	Cap D3	PA	9	Body	Aluminum
2	Piston assembly	-	10	Wiring base	-
3	Quick exhaust valve	H-NBR	11	Spool assembly	-
4	Pilot valve	-	12	Drip-proof cover	PBT
5	Manual override	PBT	13	Cap S	PA
6	Pilot valve assembly SD	-	14	Single sub-base	Aluminum
7	Decorative cover	PBT	15	Terminal block cover	PBT
8	Wiring connector	-			

Internal structure and parts list

NW4G^B_Z 420/W4GB420


● 2-position double




NW4G^B_Z 4³₄0/W4GB4³₄0

● 3-position


All ports closed



A/B/R connection





P/A/B connection



● With pilot air OFF function (M7)

* 2-position double solenoid shown in image



Main parts list

No.	Part name	Material	No.	Part name	Material
1	Cap D3	PA	9	Body	Aluminum
2	Piston assembly	-	10	Wiring base	-
3	Quick exhaust valve	H-NBR	11	Spool assembly	-
4	Pilot valve	-	12	Drip-proof cover	PBT
5	Manual override	PBT	13	Cap S	PA
6	Pilot valve assembly SD	-	14	M7 Cap	PA
7	Decorative cover	PBT	15	M7 Switch	PA
8	Wiring connector	-			

4GA/B
M4GA/B
MN4GA/B
4GA/B (master)
4GB With sensor
4GD/E
M4GD/E
MN4GD/E
4GA4/B4
MN3E
MN4E
W4GA/B2
W4GB4
MN3S0
MN4S0
4SA/B0
4KA/B
4KA/B (master)
4F
4F (master)
PV5G
GMF
PV5
GMF
PV5S-0
3Q
MV3QR
3MA/B0
3PA/B
P/M/B
NP/NAP
NVP
4G*0EJ
4F*0EX
4F*0E
HMV
HSV
2QV
3QV
SKH
Silencer
TotAirSys (Total Air)
TotAirSys (Gamma)
Ending