

# Series variation

Guided cylinder  
STG-K Series

LCM  
LCR  
LCG  
LCW  
LCX  
STM  
STG  
STS/STL  
STR2  
UCA2  
ULK\*  
JSK/M2  
JSG  
JSC3/JSC4  
USSD  
UFCD  
USC  
UB  
JSB3  
LMB  
LML  
HCM  
HCA  
LBC  
CAC4  
UCAC2  
CAC-N  
UCAC-N  
RCS2  
RCC2  
PCC  
SHC  
MCP  
GLC  
MFC  
BBS  
RRC  
GRC  
RV3\*  
NHS  
HRL  
LN  
Hand  
Chuk  
MechHnd/Chuk  
ShkAbs  
FJ  
FK  
SpdContr  
Ending

Load-resistant, shock-resistant STG-K Series

The robust guide rod is tough enough to withstand a high impact.

# Powerful

# STG-K



- More resistant to load and shock than the conventional guided cylinders.  
(Compared with our STG-M Series)
- The improved fastening mechanism combines the guide rod and end plate tightly.

Shock resistance ranked two levels higher!

**STG-K ø32**  
(Guide rod diameter 25 mm)

STG-M Series  
Covers ø32/40/50  
(Guide rod diameter 20 to 25 mm)

**STG-K ø50**  
(Guide rod diameter 30 mm)

STG-M Series  
Covers ø50/63/80  
(Guide rod diameter 25 to 30 mm)