

JSM2/JSK2/JSC3/JSC4 Series

* Related product selection guide

Overrun distance and stopping accuracy differ depending on the used valve. Use the following related products.

Model	Related products Bore size (mm)	SOL-1	SOL-2	Reverse regulator	Speed controller	Silencer	Piping
JSM2 JSK2	ø20	4GB150R-06	3GA110R	R1100-6-W 2419-1C	SC3W-6-6 SC3R-6 SC1-6	SLW-6A	ø6×ø4 Nylon tube
JSK2	ø25	4GB150R-06	3GA110R	R1100-6-W 2419-1C	SC3W-6-6 SC3R-6 SC1-6	SLW-6A	ø6×ø4 Nylon tube
JSM2	ø30	4GB150R-06 4GA210R-06 4GB250R-06	3GA110R	R1100-6-W 2419-1C	SC3W-6-6 SC3R-3-6 SC1-6	SLW-6A	ø6×ø4 Nylon tube
JSK2	ø32	4GB150R-06 4GA250R-06 4GB250R-06	B5136	R1100-6-W 2419-1C	SC3W-6-6 SC3R-3-6 SC1-6	SLW-6A	ø6×ø4 Nylon tube
JSM2 JSK2	ø40	4GA250R-06 4GB250R-06	4GA110R-06 4GB110R-06	R1100-6-W 2419-1C	SC3W-6-8 SC3R-6 SC1-6	SLW-6A	ø8×ø5.7 Nylon tube
JSC3	ø40	4GB250R-08 4GB350R-08 PV5G-6-FIG-D-1-A02	4GA210R-06 4GB210R-06	R3100-8-W R2100-8-W	SC3W-8-8 SC3R-8 SC1-8	SLW-8A	ø8×ø5.7 Nylon tube
	ø50	4GA350R-08 4GB350R-10 PV5G-6-FIG-D-1-A03	4GA210R-06 4GB210R-08	R3100-10-W R2100-10-W	SC3W-10-10 SC3R-10 SC1-10	SLW-10A	ø10×ø7.2 Nylon tube
	ø63	4GB350R-08 4GB350R-10 PV5G-6-FIG-D-1-A03	4GA210R-06 4GB210R-08	R4100-10-W	SC3W-10 SC3R-10 SC1-10	SLW-10A	ø10×ø7.2 Nylon tube
	ø80	4GB450-15 PV5G-8-FIG-D-1-A04	4GA210R-06 4GB210R-08	R4100-15-W	SC3W-15-12 SC3R-15 SC1-15	SLW-15A	ø12×ø8.9 Nylon tube
	ø100	4GB450-15 PV5G-8-FIG-D-1-A04	4GB310R-10	R4100-15-W	SC3W-15-12 SC3R-15 SC1-15	SLW-15A	ø12×ø8.9 Nylon tube
JSC4	ø125	4GB450-15 PV5G-8-FIG-D-1-A04	4GB310R-10 4F310R-10	R4100-15-W	SC3R-15 SC1-15	SLW-15A	ø12 rubber hose SGP3/8B SGP1/2B
	ø140	4F650-20	4GB310R-10 4F310R-10	R4100-15-W-A20W R6100-20-W	SC-20A	SL-20A	ø19 rubber hose SGP1/2B SGP3/4B
	ø160	4F650-20 4F750-20	4GB310R-10 4F310R-10	R4100-15-W-A20W R6100-20-W	SC-20A	SL-20A	ø19 rubber hose SGP1/2B SGP3/4B
	ø180	4F750-20	4GA410-10 4GB410-10 4F310-10	R4100-15-W-A20W R6100-20-W	SC-20A	SL-20A	ø19 rubber hose SGP1/2B SGP3/4B

● *1: JSC3-V is assembled with a brake release valve (SOL2).