

How to order

Without switch (built-in magnet for switch)

STM - M - 10 - 15 - A - P4 P40

With switch (built-in magnet for switch)

STM - M - 10 - 15 - SW83 - D - A - P4 P40

A Bearing

B Bore size

C Stroke

D Switch model No.
*1

E Switch quantity

F Option

Code	Item
A Bearing	
M	Metal bush bearing
B	Ball bearing

B Bore size (mm)	
6	ø6
10	ø10

C Stroke (mm)		Bore size	
		6	10
5	5	●	●
10	10	●	●
15	15	●	●
20	20		●

D Switch model No.	
Refer to the compatibility table on Intro Pages 23 to 26 for switch model No.	

E Switch quantity	
R	1 on rod side
H	1 on head side
D	2

F Option	
A	Side mounting
R	Rear piping

⚠ Precautions for model No. selection

*1: When using a 2-color display proximity switch for STM-B-6, avoid mounting the cylinder on a magnetic substance such as a metal plate. This could lead to switch detection malfunction.

Related products

Speed controller								
Model No.	Appearance	Port size (Rc or R)			Compatible tube O.D.			Page
		M3	M5	1/8	4(ø4)	6(ø6)	8(ø8)	
SC3W-M3- *-P4		●			●			530
SC3W-M5- *-P4			●		●	●		

Specify the compatible tube O.D. code for *.

P4
Series

Pneumatic actuator
Hand/Chuck
Related products
Cylinder
Switch

Vacuum components

Pneumatic valves
Clean air components

Pneumatic auxiliary components
Speed controller

Fitting
Auxiliary valve
Silencer
Tube

Gas generator

Fluid control components

Motor specification

Motorless specifications