

Selection guide

: Not applicable
 Port size column
○ : Rp ● : JIS flange
▲ : DIN flange ● : Rp and JIS flange

Series name			Working pressure			Compatible with hydrogen gas	Opening operation		Port size													Description Page				
			Low pressure	Intermediate pressure	Medium pressure		Quick	Slow	8A	15A	20A	25A	32A	40A	50A	65A	80A	100A	125A	150A	200A		250A			
									1/4	1/2	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4	5	6	8		10			
Gas combination valve	GHV		○	○		○	○	○					○	○	○	○										3
	GRV		○	○	○	○		○																		7
Solenoid valve	DSG		○			○	○						○	○												9
	DSG-W		○			○	○						○	○												13
	VNA		○	○		○	○						○	○	○	○	○									15
	VLA		○	○		○		○					○	○	○	○	○									21
	VNA-R/RH		○	○	○	○	○						○	○	○											25
	VNR		○	○		○	○							○	○	○	○									29
Medium pressure gas Safety shutoff Control system	TAC-25				○		○	○																		31
	VNM		○	○	○	○	○							●												35
	VLM		○	○	○	○		○						●												37
	C25N-B				○									●												39
Safety residual pressure exhaust valve	VNM-25-K		○	○	○		○						●												41	
Motorized valve	HK1		○	○	○	○		○							●	●	●	●	▲	▲	▲	▲				43
	HS		○	○	○	○		○							●											47