

Pneumatic Components

To Use This Product Safely

Be sure to read this before use.

For general pneumatic components precautions, Intro 15 for details.

Individual Precautions: Suction Pad Soft Type, VSP-□L□Series

Design / Selection



■The VPHC type holder is not conductive. When using suction pads made of conductive material, take measures to discharge electricity directly from the pad rubber.

•When replacing the pad adapter of the soft type, check the suction pad configuration diagram in the main text, refer to the recommended tightening torque below, use appropriate tools, utilize the holder outer diameter hexagonal part, and confirm there is no looseness after tightening.

■Recommended Tightening Torque

| Pad Thread Size (mm) | Tightening Torque |
|----------------------|-------------------|
| M4x0.7 | 0.7 to 0.8 N·m |
| M6x1 | 1.5 to 2.0 N·m |

Standard

Bellows

Multistage Bellows

Oblong

Non-slip

Workpiece

Flat

Suction Mark Prevention

For Packaging Bags

For Metal

Ending

MEMO

Standard

Oblong

Soft Bellows

Workpiece

Flat

For Packaging Bags

For Metal

CKD