

General Type

Features	Model No./Appearance	Bore Size ø (mm)							Bore Size ø (mm)																	
		2.5	4	6	8	10	12	15	16	20	25	30	32	40	50	63	80	100	125	140	160	180	200	250		
		Max. Stroke (mm) (Producible Stroke (mm)) *1																								
General Type	Pencil shaped compact cylinder 	10	20	100 (105)		200 (210)			260 (270)																	
	Stainless steel tube adopted Crimped Type 									750			750													
	Maintainable dismountable type 									700 (1000)		700 (1200)		700 (1500)												
	Abundant variations Most compact among general types 									1,000		1,000		1,500												
	Tie Rod	Compact type among tie rods 														600 (700)		700 (1400)		800 (1500)						
		Robust type with No. 1 reliability Abundant variations 															600 (1600)		700 (2,000)		800 (2,500)					
		Compatible with ø125 and above 																				800		900	1,000	1,200

*1: Bore Size and Stroke represent typical models. For details, refer to the catalog specifications.

General Type

SCP3

CMK2

CMA2

SCM

SCG

SCA2

SCS2

Cylinder Switch

Ending

General Type

SCP3

CMK2

CMA2

SCM

SCG

SCA2

SCS2

Cylinder Switch

Ending

