

Series variation



Micro cylinder CMA2 series

SCP*3	variation														
CMK2	CMA2 series														
CMA2	Variation	Model No. JIS symbol	Bore size (mm)	Standard stroke (mm)								(mm) Min. stroke	(mm) Max. stroke	(mm) Available stroke	
SCM															
SCG															
SCA2															
SCS2															
CKV2															
CAV2/ COVPIN2															
SSD2	Double acting/ single rod	CMA2 	ø20 ø30 ø40	●	●	●	●	●	●	●	●	1	700	1000 1200 1500	
SSG															
SSD	Double acting/ direct	CMA2-E 	ø20/ø30/ø40	●	●	●	●	●	●	●	●	1	700	700	
CAT															
MDC2															
MVC															
SMG															
MSD/ MSDG															
FC*															
STK															
SRL3															
SRG3															
SRM3															
SRT3															
MRL2															
MRG2															
SM-25															
ShkAbs															
FJ															
FK															
Spd Contr															
Ending															

●: Standard, ◎: Option, ○: Made to order, ■: Not available

	Custom stroke (per mm)	Mounting									Option					Accessory			Switch	Page
		Basic	Axial foot Two sides	Axial foot One side	Rod side flange	Head side flange	Eye bracket	Clevis bracket	Rod side trunnion	Head side trunnion	Bellows (100°C)	Bellows (250°C)	Piston rod material change	Same port position	Copper and PTFE free	Rod eye	Rod clevis	Clevis bracket		
		00	LB	LS	FA	FB	CA	CB	TA	TB	J	L	M	P	P6	I	Y	B2		
	1	●	●	●	●	●	●	●	●	◎	◎	◎	◎	◎	◎	◎	◎	◎	◎	208
	1			●	●							◎			◎	◎	◎	◎	◎	222

SCP*3
CMK2
CMA2
SCM
SCG
SCA2
SCS2
CKV2
CAV2/ COVP/IN2
SSD2
SSG
SSD
CAT
MDC2
MVC
SMG
MSD/ MSDG
FC*
STK
SRL3
SRG3
SRM3
SRT3
MRL2
MRG2
SM-25
ShkAbs
FJ
FK
Spd Contr
Ending