

Series variation



Compact cylinder SSG Series

●: Standard, ◎: Option, ■: Not available

Variation	Model No. JIS symbol	Bore size (mm)	Stroke (mm)												Max. stroke (mm)	Min. stroke (mm)	Switch	Page
			5	10	15	20	25	30	35	40	45	50	75	100				
With double acting/ single rod switch, with 2-color LED, off-delay, T1 switch	SSG SSG-L SSG-L1	ø12/ø16	●	●	●	●	●	●	■	■	■	■	■	■	30	1	◎	1068
		ø20/ø25	●	●	●	●	●	●	●	●	●	●	■	■	50			
		ø32/ø40	●	●	●	●	●	●	●	●	●	●	●	●	100			
		ø50/ø63/ø80/ø100	■	●	●	●	●	●	●	●	●	●	●	●	100			

SCP*3

CMK2

CMA2

SCM

SCG

SCA2

SCS2

CKV2

CAV2/
COVP/N2

SSD2

SSG

SSD

CAT

MDC2

MVC

SMG

MSD/
MSDG

FC*

STK

SRL3

SRG3

SRM3

SRT3

MRL2

MRG2

SM-25

ShkAbs

FJ

FK

Spd
Contr

Ending