


Series variation



High precision guided rodless cylinder SRM3 Series

SCP*3
CMK2
CMA2
SCM
SCG
SCA2
SCS2
CKV2
CAV2/ COVPIN2
SSD2
SSG
SSD
CAT
MDC2
MVC
SMG
MSD/ MSDG
FC*
STK
SRL3
SRG3
SRM3
SRT3
MRL2
MRG2
SM-25
ShkAbs
FJ
FK
Spd Contr
Ending

Variation	Model No. JIS symbol	Bore size (mm)	Standard stroke (mm)												
			200	300	400	500	600	700	800	900	1000	1100	1200	1300	1400
Double acting	SRM3 	ø25 equivalent/ ø32 equivalent	●	●	●	●	●	●	●	●	●				
		ø40 equivalent/ ø63 equivalent	●	●	●	●	●	●	●	●	●	●	●	●	
Double acting/ position locking	SRM3-Q	ø25 equivalent/ ø32 equivalent	●	●	●	●	●	●	●	●	●				
		ø40 equivalent/ ø63 equivalent	●	●	●	●	●	●	●	●	●	●	●	●	

●: Standard, ◎: Option, ■: Not available

Standard stroke (mm)							Min. stroke (mm)	Max. stroke (mm)	Custom stroke (per mm)	Cushion				Option								Switch	Page
										Without cushion	Both sides cushioned	R side cushioned	L side cushioned	Both side full stroke adjustable with shock absorber	R side full stroke adjustable with shock absorber	L side full stroke adjustable with shock absorber	Full stroke adjustable with adjusting bracket to be added later	Both side full stroke adjustable with light-load shock absorber	R side full stroke adjustable with light-load shock absorber	L side full stroke adjustable with light-load shock absorber	Copper and PTFE free		
	1500	1600	1700	1800	1900	2000				N	B	R	L	A	A1	A2	A3	E	E1	E2	P6		
							50	1000	1	●	●	●	●	⊙	⊙	⊙	⊙	⊙	⊙	⊙	●	⊙	1676
	●	●	●	●	●	●	80	2000		●	●	●	●	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	●	
							50	1000	1	●	●	●	●	⊙	⊙	⊙	⊙	⊙	⊙	⊙	●	⊙	1676
	●	●	●	●	●	●	80	2000		●	●	●	●	⊙	⊙	⊙	⊙	⊙	⊙	⊙	⊙	●	

SCP*3
CMK2
CMA2
SCM
SCG
SCA2
SCS2
CKV2
CAV2/ COVP/IN2
SSD2
SSG
SSD
CAT
MDC2
MVC
SMG
MSD/ MSDG
FC*
STK
SRL3
SRG3
SRM3
SRT3
MRL2
MRG2
SM-25
ShkAbs
FJ
FK
Spd Contr
Ending