

Series variation



Magnet rodless cylinder high precision guide MRG2 Series

●: Standard, ◎: Option, ■: Not available

Variation	Model No.	Bore size (mm)	Standard stroke (mm)									Min. stroke (mm)	Max. stroke (mm)	Option			Switch	Page
														With both-sided full stroke, adjustable brackets	With R side full stroke, adjustable bracket	With L side full stroke, adjustable bracket		
			50	100	150	200	300	400	500	600	700			A	A1	A2		
Double acting	MRG2 	ø10	●	●	●	●	●					50	300				◎	1766
		ø16	●	●	●	●	●	●			500		◎	◎	◎			
		ø25	●	●	●	●	●	●	●	●	700							

SCP*3
CMK2
CMA2
SCM
SCG
SCA2
SCS2
CKV2
CAV2/COVP/IN2
SSD2
SSG
SSD
CAT
MDC2
MVC
SMG
MSD/MSDG
FC*
STK
SRL3
SRG3
SRM3
SRT3
MRL2
MRG2
SM-25
ShkAbs
FJ
FK
Spd Contr
Ending