



Series variation



Linear slide cylinder LCW Series

- LCM
- LCR
- LCG
- LCW**
- LCX
- STM
- STG
- STS/STL
- STR2
- UCA2
- ULK*
- JSK/M2
- JSG
- JSC3/JSC4
- USSD
- UFCD
- USC
- UB
- JSB3
- LMB
- LML
- HCM
- HCA
- LBC
- CAC4
- UCAC2
- CAC-N
- UCAC-N
- RCS2
- RCC2
- PCC
- SHC
- MCP
- GLC
- MFC
- BBS
- RRC
- GRC
- RV3*
- NHS
- HRL
- LN
- Hand
- Chuk
- MecHnd/Chuk
- ShkAbs
- FJ
- FK
- SpdContr
- Ending

● : Standard ○ : Option ■ : Not available

Variation	Model No. JIS symbol	Bore size (mm)	Stroke length (mm)			Stopper					Switch	Page
						Cushion stopper	Rubber cushion long stopper	Metal stopper with rubber cushion	Metal long stopper with rubber cushion	Shock absorber stopper		
			30	50	75	Blank	S	M	MS	A		
Double acting/ single rod	LCW 	ø12	●	●	●	●	○	○	○	○	○	204
		ø16	●	●	●	●	○	○	○	○	○	
		ø20	●	●	●	●	○	○	○	○	○	
Double acting/ position locking	LCW-Q 	ø12	●	●	●	●	○	○	○	○	○	224
		ø16	●	●	●	●	○	○	○	○	○	
		ø20	●	●	●	●	○	○	○	○	○	