




Series variation



Linear slide cylinder LCR Series


LCM
LCR
 LCG
 LCW
 LCX
 STM
 STG
 STS/STL
 STR2
 UCA2
 ULK*
 JSK/M2
 JSG
 JSC3/JSC4
 USSD
 UFCD
 USC
 UB
 JSB3
 LMB
 LML
 HCM
 HCA
 LBC
 CAC4
 UCAC2
 CAC-N
 UCAC-N
 RCS2
 RCC2
 PCC
 SHC
 MCP
 GLC
 MFC
 BBS
 RRC
 GRC
 RV3*
 NHS
 HRL
 LN
 Hand
 Chuk
 MecHnd/Chuk
 ShkAbs
 FJ
 FK
 SpdContr
 Ending

Variation	Model No. JIS symbol	Bore size (mm)	Stroke length (mm)									
			10	20	30	40	50	75	100	125	150	
Double acting/ single rod	LCR 	ø6	●	●	●	●	●					
		ø8	●	●	●	●	●	●				
		ø12	●	●	●	●	●	●	●			
		ø16	●	●	●	●	●	●	●	●		
		ø20/ø25	●	●	●	●	●	●	●	●	●	
Double acting/ position locking	LCR-Q 	ø8	●	●	●	●	●	●				
		ø12	●	●	●	●	●	●	●			
		ø16	●	●	●	●	●	●	●	●		
		ø20/ø25	●	●	●	●	●	●	●	●	●	
Double acting/ single rod clean-room specifications	LCR-P7* 	ø6	●	●	●	●	●					
		ø8	●	●	●	●	●	●				
		ø12	●	●	●	●	●	●	●			
		ø16	●	●	●	●	●	●	●	●		
		ø20/ø25	●	●	●	●	●	●	●	●	●	
Double acting/ fine speed	LCR-F 	ø12	●	●	●	●	●	●	●			
		ø16	●	●	●	●	●	●	●	●		
		ø20/ø25	●	●	●	●	●	●	●	●	●	
Double acting/ fine speed clean-room specifications	LCR-F-P7* 	ø12	●	●	●	●	●	●	●			
		ø16	●	●	●	●	●	●	●	●		
		ø20/ø25	●	●	●	●	●	●	●	●	●	

●: Standard, ◎: Option, ○: Made to order, ■: Not available

	Option																							Switch	Page		
	Stroke adjusting stopper						Shock absorber stopper						Two-sided combined double stopper						One side hybrid stopper mix				With buffer				
	Stopper position ①	Stopper position ②	Stopper position ③	Stopper position ④	Stopper position ①/③	Stopper position ②/④	Stopper position ①	Stopper position ②	Stopper position ③	Stopper position ④	Stopper position ①/③	Stopper position ②/④	A1 + metal stopper	A2 + metal stopper	A3 + metal stopper	A4 + metal stopper	A5 + metal stopper	A6 + metal stopper	A1 + S3	A2 + S4	A3 + S1	A4 + S2	Without switch groove			With switch groove	Plug attached
	S1	S2	S3	S4	S5	S6	A1	A2	A3	A4	A5	A6	W1	W2	W3	W4	W5	W6	C1	C2	C3	C4	B	BL	N		
	◎	◎	◎	◎	◎	◎	◎	◎	◎	◎	◎	◎	○	○	○	○	○	○	○	○	○	○	◎	◎	◎		
	◎	◎					◎	◎					○	○									○	○	◎		
	◎	◎	◎	◎	◎	◎																			◎		
	◎	◎	◎	◎	◎	◎	◎	◎	◎	◎	◎	◎	○	○	○	○	○	○	○	○	○	○			◎		
	◎	◎	◎	◎	◎	◎																			◎		
																									◎		
																									◎		

● Stopper position



LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending