






Series variation

Linear slide cylinder LCM Series

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MecHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending

Variation	Model No. JIS symbol	Bore size (mm)	
Double acting/single rod	LCM 	ø4.5	
		ø6	
		ø8	
Double acting/stroke adjustable (Push)	LCM-P 	ø4.5	
		ø6	
		ø8	
Double acting/stroke adjustable (push/pull)	LCM-R 	ø4.5	
		ø6	
		ø8	
Double acting/side mounting	LCM-A 	ø4.5	
		ø6	
		ø8	
Double acting/single rod clean-room specifications	LCM-P73 	ø4.5	
		ø6	
		ø8	

●: Standard, ◎: Option, ○: Made to order, ■: Not available

	Standard stroke (mm)					Option				Switch	Page
						With buffer	With magnet	With magnet + switch rail	With positioning pin		
	5	10	15	20	30	B	M	F	J*		
	●	●	■	■	■	◎	◎	◎	◎	◎	10
	●	●	●	●	●						
	●	●	●	●	●						
	●	●	■	■	■	◎	◎	◎	◎	◎	18
	●	●	●	●	●						
	●	●	●	●	●						
	●	●	■	■	■	◎	◎	◎	◎	◎	24
	●	●	●	●	●						
	●	●	●	●	●						
	●	●	■	■	■	◎	◎	◎	◎	◎	30
	●	●	●	●	●						
	●	●	●	●	●						
	●	●	■	■	■	■	◎	◎	◎	◎	40
	●	●	●	●	●						
	●	●	●	●	●						

Note : Custom stroke is not available.

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending