



Series variation

Guided cylinder STM Series

LCM
 LCR
 LCG
 LCW
 LCX
STM
 STG
 STS/STL
 STR2
 UCA2
 ULK*
 JSK/M2
 JSG
 JSC3/JSC4
 USSD
 UFCD
 USC
 UB
 JSB3
 LMB
 LML
 HCM
 HCA
 LBC
 CAC4
 UCAC2
 CAC-N
 UCAC-N
 RCS2
 RCC2
 PCC
 SHC
 MCP
 GLC
 MFC
 BBS
 RRC
 GRC
 RV3*
 NHS
 HRL
 LN
 Hand
 Chuk
 MecHnd/Chuk
 ShkAbs
 FJ
 FK
 SpdContr
 Ending

Variation	Model No. JIS symbol	Bore size (mm)	Stroke length (mm)				
			5	10	15	20	
Double acting/single rod	STM-M/B 	ø6	●	●	●		
		ø10	●	●	●	●	
Double acting/single rod clean-room specifications	STM-B-P7* 	ø6	●	●	●		
		ø10	●	●	●	●	

● : Standard, ◎ : Option, ■ : Not available

	Max. stroke length (mm)	Bearing		Option		Switch	Page
		Metal bush bearing M	Ball bearing B	Side mounting A	Rear piping R		
	15	●	●	●	●	◎	314
	20	●	●	●	●	◎	
	15	■	●	●	■	◎	320
	20	■	●	●	■	◎	

LCM
 LCR
 LCG
 LCW
 LCX
 STM
 STG
 STS/STL
 STR2
 UCA2
 ULK*
 JSK/M2
 JSG
 JSC3/JSC4
 USSD
 UFCD
 USC
 UB
 JSB3
 LMB
 LML
 HCM
 HCA
 LBC
 CAC4
 UCAC2
 CAC-N
 UCAC-N
 RCS2
 RCC2
 PCC
 SHC
 MCP
 GLC
 MFC
 BBS
 RRC
 GRC
 RV3*
 NHS
 HRL
 LN
 Hand
 Chuk
 MechHnd/Chuk
 ShkAbs
 FJ
 FK
 SpdContr
 Ending