


●: Standard, ○: Option

Variation	Model No. JIS symbol	Bore size (mm)	Standard stroke length (mm)							Min. stroke length (mm) *1	Max. stroke length (mm)	Custom stroke length (per mm) *2	Switch	Page
			25	50	75	100	125	150	175					
Double acting/ guide rod	STG-K 	ø32/ø50	●	●	●	●	●	●	●	5 (10)	200	5	○	432

*1 : The value in () for min. stroke length is for switches of the 2-color display and AC magnetic field proof.

*2 : Custom stroke is handled by attaching a spacer to the standard stroke length cylinder.

For dedicated bodies corresponding to stroke length, contact CKD separately.

- LCM
- LCR
- LCG
- LCW
- LCX
- STM
- STG**
- STS/STL
- STR2
- UCA2
- ULK*
- JSK/M2
- JSG
- JSC3/JSC4
- USSD
- UFCD
- USC
- UB
- JSB3
- LMB
- LML
- HCM
- HCA
- LBC
- CAC4
- UCAC2
- CAC-N
- UCAC-N
- RCS2
- RCC2
- PCC
- SHC
- MCP
- GLC
- MFC
- BBS
- RRC
- GRC
- RV3*
- NHS
- HRL
- LN
- Hand
- Chuk
- MechHnd/Chuk
- ShkAbs
- FJ
- FK
- SpdContr
- Ending