



Series variation



Tie rod cylinder with brake JSG Series

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MecHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending

Variation	Model No. JIS symbol	Bore size (mm)	Standard stroke (mm)												Min. stroke	
			25	50	75	100	150	200	250	300	350	400	450	500		
Double acting/ single rod	JSG 	ø40													1	
		ø50/ø63	●	●	●	●	●	●	●	●	●	●	●			
		ø80														
		ø100														
Double acting/ with valve for brake release	JSG-V 	ø40													1	
		ø50/ø63	●	●	●	●	●	●	●	●	●	●	●			
		ø80														
		ø100														

●: Standard, ◎: Option, ○: Made to order, ■: Not available

	Max. stroke		Available stroke		Custom stroke	Mounting								Cushion		Option		Accessory						Switch	Page	
						Basic	Axial foot	Rod side flange	Head side flange	Eye bracket	Clevis bracket	Rod side trunnion	Head side trunnion	Intermediate trunnion	Two-sided air cushion	Two-sided rubber cushion	Bellows (100°C)	Piston rod material stainless steel	Rod eye	Rod clevis	Eye bracket	Clevis bracket	Eye bracket			Trunnion No. 2 bracket
	600	800	1	●	●	●	●	●	●	●	●	●	●	◎	◎	◎	◎	◎	◎	◎	◎	◎	◎	◎	742	
	700	1400																								
	800	1500																								
	600	800	1	●	●	●	●	●	●	●	●	●	●		◎	◎	◎	◎	◎	◎	◎	◎	◎	◎	742	
	700	1400																								
	800	1500																								

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending