


Series variation



Position locking compact cylinder USSD Series

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MecHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending

Variation	Model No. JIS symbol	Bore size (mm)	Standard stroke (mm)						
			5	10	15	20	25	30	
Double acting with switch	USSD USSD-L 	ø20	●	●	●	●	●	●	
		ø25/ø32/ø40/ø50	●	●	●	●	●	●	
		ø63/ø80/ø100	●	●		●		●	
Double acting/high load with switch	USSD-K USSD-KL 	ø20	●	●	●	●	●	●	
		ø25/ø32/ø40/ø50		●	●	●	●	●	
		ø63/ø80/ø100		●		●		●	

●: Standard ◎: Option ■: Not available

Stroke (mm)								Min. stroke (mm)	Max. stroke (mm)	Custom stroke (per mm)	Option	Mounting bracket		Switch	Page
	40	50	60	70	80	90	100				Rod end male thread	Foot	Clevis bracket		
								1	30	1	◎	◎	◎	◎	846
	●	●							50		◎	◎	◎		
	●	●							50		◎	◎	◎		
	●	●						1	200	1	◎	◎	◎	◎	846
	●	●	●	●	●	●	●		300		◎	◎	◎		
	●	●	●	●	●	●	●		300		◎	◎	◎		

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending