

Series variation



Mechanical power cylinder MCP Series

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MecHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending

Variation	Model No.	Effective thrust (Thrust at 0.6 MPa)	Stroke (mm)	
Rapid feed + booster	MCP-W	For 2t/5t	50/100/150/200/250/300/350/400/450/500	
Booster section only	MCP-S	For 2t/5t	10	

●: Standard ○:Option

	Min. stroke	Max. stroke	Mounting		Option	Page
			Basic	Rod side flange	Rod end male thread	
	(mm)	(mm)	00	FA	N	
	50	500	●	●	○	1180
	-	-	●	●	○	

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending