


Series variation



High rigid guideless cylinder GLC Series

- LCM
- LCR
- LCG
- LCW
- LCX
- STM
- STG
- STS/STL
- STR2
- UCA2
- ULK*
- JSK/M2
- JSG
- JSC3/JSC4
- USSD
- UFCD
- USC
- UB
- JSB3
- LMB
- LML
- HCM
- HCA
- LBC
- CAC4
- UCAC2
- CAC-N
- UCAC-N
- RCS2
- RCC2
- PCC
- SHC
- MCP
- GLC**
- MFC
- BBS
- RRC
- GRC
- RV3*
- NHS
- HRL
- LN
- Hand
- Chuk
- MecHnd/Chuk
- ShkAbs
- FJ
- FK
- SpdContr
- Ending

Variation	Model No.	Bore size (mm)	Standard stroke length (mm)					
			100	200	300	400	500	
Double acting	GLC	ø40/ø50/ø63	●	●	●	●	●	
		ø80	●	●	●	●	●	
		ø100	●	●	●	●	●	

● : Standard, ○ : Option, ■ : Not available

Stroke length (mm)				Min. stroke length (mm)	Max. stroke length (mm)	Custom stroke length (per mm)	Mounting				Rod end form			Piping port position				Switch	Page
							Basic	Axial foot	Rod side flange	Head side flange	Female thread	Male thread	Flange	Top from rod side	Right from rod side	Left from rod side	Bottom from rod side		
600	700	800	(mm)	(mm)	(per mm)	00	LB	FA	FB	Blank	N	F	Blank	R	T	S			
■	■	■	5	500	5	●	●	●	●	●	○	○	●	○	○	○	○	○	1198
●	●	●		700															
●	●	●		800															

- LCM
- LCR
- LCG
- LCW
- LCX
- STM
- STG
- STS/STL
- STR2
- UCA2
- ULK*
- JSK/M2
- JSG
- JSC3/JSC4
- USSD
- UFCD
- USC
- UB
- JSB3
- LMB
- LML
- HCM
- HCA
- LBC
- CAC4
- UCAC2
- CAC-N
- UCAC-N
- RCS2
- RCC2
- PCC
- SHC
- MCP
- GLC**
- MFC
- BBS
- RRC
- GRC
- RV3*
- NHS
- HRL
- LN
- Hand
- Chuk
- MechHnd/Chuk
- ShkAbs
- FJ
- FK
- SpdContr
- Ending