

Series variation

Air operated 2, 3-port valve (coolant control) (coolant valve)

EXA
FWD
HNB/G
USB/G
FAB/G
FGB/G
FVB
FWB/G
FHB
FLB
AB
AG
AP/ AD
APK/ ADK
DryAir
EX- XPLNprf
XPLNprf
HVB/ HVL
S ◇ B/ NAB
LAD/ NAD
Water- Rela
NP/NAP/ NVP
SNP
CHB/G
MXB/G
Other valves
SWD/ MWD
DustColl
CVE/ CVSE
CCH/ CPE/D
LifeSci
Gas- Combus
Auto- Water
Outdoor
SpecFld
Custom
Ending

Number of ports	Classification			Model	Configuration	Working pressure MPa			
							Rc3/8	Rc1/2	
2-port		For low pressure	Air operated	CVE2-***-05	Single unit	0 to 0.5	●	●	
			With solenoid valve	CVSE2-***-05			●	●	
			Air operated	CVE2-***-10		0 to 1.0	●	●	
			With solenoid valve	CVSE2-***-10			●	●	
		For medium pressure	Air operated	CVE2-***-16		0 to 1.6	●	●	
			With solenoid valve	CVSE2-***-16			●	●	
			Air operated	CVE2-***-30		0 to 3.0	●	●	
			With solenoid valve	CVSE2-***-30			●	●	
		For high pressure	Air operated	CVE2-***-70		0 to 7.0	●	●	
			With solenoid valve	CVSE2-***-70			●	●	
		For low pressure	Air operated	GCVE2-***-05	Module	0 to 0.5		●*	
			With solenoid valve	GCVSE2-***-05				●*	
			Air operated	GCVE2-***-10		0 to 1.0		●*	
			With solenoid valve	GCVSE2-***-10				●*	
		For medium pressure	Air operated	GCVE2-***-16		0 to 1.6		●*	
			With solenoid valve	GCVSE2-***-16				●*	
3-port		For low pressure	Air operated	CV3E-***-03	Single unit	0 to 0.3			
			With solenoid valve	CVS3E-***-03					
		For medium pressure	Air operated	CVE3-***-35		0 to 3.5	●	●	
			With solenoid valve	CVSE3-***-35			●	●	
		For high pressure	Air operated	CVE3-***-70		0 to 7.0	●	●	
			With solenoid valve	CVSE3-***-70			●	●	

	Port size										Page
	Rc3/4	Rc1	Rc1 ^{1/4}	32 flange	Rc1 ^{1/2}	40 flange	Rc2	50 flange	65 flange	80 flange	
	●	●	●	●	●	●	●	●	●	●	856
	●	●	●	●	●	●	●	●	●	●	856
	●	●	●	●	●	●	●	●	●	●	856
	●	●	●	●	●	●	●	●	●	●	856
	●	●									866
	●	●									866
	●	●									866
	●	●									866
	●	●									874
	●	●									874
	●*										894
	●*										894
	●*										894
	●*										894
	●*										894
	●*										894
	●	●									892
	●	●									892
	●	●	●		●		●				880
	●	●	●		●		●				880
	●	●									880
	●	●									880

* OUT port size

EXA
FWD
HNB/G
USB/G
FAB/G
FGB/G
FVB
FWB/G
FHB
FLB
AB
AG
AP/ AD
APK/ ADK
DryAir
EX- XPLNprf
XPLNprf
HVB/ HVL
S [◇] B/ NAB
LAD/ NAD
Water- Rela
NP/NAP/ NVP
SNP
CHB/G
MXB/G
Other valves
SWD/ MWD
DustColl
CVE/ CVSE
CCH/ CPE/D
LifeSci
Gas- Combus
Auto- Water
Outdoor
SpecFld
Custom
Ending