

F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain
Separ
Mech
Press SW
Res press
exh valve
SlowStart
Anti-bac/Bac-
remove Filt
Film
Resist FR
Oil-ProhR
Med
Press FR
No Cu/
PTFE FRL
Outdrs FRL
Adapter
Joiner
Press
Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneR
AirBoost
Speed Ctrl
Silncr
CheckV/
other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro
Press SW
ContactSW
AirSens
PresSW
Cool
Air Flo
Sens/Ctrl
WaterRtSens
TotAirSys
(Total Air)
TotAirSys
(Gamma)
Gas
generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg
etc
Ending

GW Fitting

Port size M3 to 1/2 (Rc or R)

● Wide connection fittings and models.



Straight									
Single straight/ GWS□-□		Single straight/ GWS□-□-S		Female straight/ GWS□-□-M		Bulkhead female/ GWS□-□-E		Bulkhead/ GWS□-□-X	
	Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø
	4		3.2		4		4		4
	6		4		6		6		6
	8		6		8		8		8
	10		8		10		10		10
	12		10		12		12		12
·Refer to page: 828		·Refer to page: 828		·Refer to page: 828		·Refer to page: 828		·Refer to page: 829	
Bulkhead female connector/ GWM□-□-X		Straight/ GWS□-0		Different diameter straight/ GWS□-0		Plug reducer/ GWS□-□P		Plug/ GWP□-0	
	Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø		Fitting port size ø
	4		4		4/6		4		4
	6		6		6/8		6		6
	8		8		8/10		8		8
	10		10		10/12		10		10
	12		16						12
·Refer to page: 829		·Refer to page: 829		·Refer to page: 829		·Refer to page: 830		·Refer to page: 830	
Elbow									
Plug reducer/ GWP□-0		Single elbow/ GWL□-□		Long elbow/ GWL□-□-L		Single 45° elbow/ GWL□-□-45		Turn elbow/ GWL□-□-T	
	Fitting port size ø		Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø
	4/6		4		4		4		4
	6/8		6		6		6		6
	8/10		8		8		8		8
	10/12		10		10		10		10
			12		12		12		12
·Refer to page: 830		·Refer to page: 830		·Refer to page: 831		·Refer to page: 831		·Refer to page: 831	
Tee									
Elbow/ GWL□-0		Double tee/ GWT□-□		D tee/ GWT□-□-D		Tee/ GWT-0		Y tee/ GWY□-0	
	Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø
	4		4		4		4		4/4
	6		6		6		6		6/6
	8		8		8		8		8/8
	10		10		10		10		10/10
	12		12		12		12		12/12
·Refer to page: 831		·Refer to page: 832		·Refer to page: 832		·Refer to page: 832		·Refer to page: 832	
								6/4	
								8/6	
								10/8	
								12/10	

Double Y tee/ GWY□-□	Cross/ GWCR□-0	2-port turn elbow/ GWL□-□-2T	Tetrapod (with R)/ GWTR□-□	FY (with R)/ GWFY□-□
 Compatible tube O.D. ø 4 6 8 10 12	 Compatible tube O.D. ø 8 10 12	 Compatible tube O.D. ø 4 6 8 10 12	 Compatible tube O.D. ø 4 6 8 10 12	 Compatible tube O.D. ø 4 6 8 10 12
·Refer to page: 833	·Refer to page: 833	·Refer to page: 833	·Refer to page: 833	·Refer to page: 834
Double Y (with R)/ GWWY□-□	Tetrapod/ GWTR□-0	FY/ GWFY□-0	Double Y/ GWWY□-0	Blanking plug/ GWP□-B
 Compatible tube O.D. ø 4 6	 Compatible tube O.D. ø 4 6 8 10 12	 Compatible tube O.D. ø 4 6 8 10 12	 Compatible tube O.D. ø 6/4 8/6	 Fitting port size ø 4 6 8 10 12 16
·Refer to page: 834	·Refer to page: 834	·Refer to page: 834	·Refer to page: 835	·Refer to page: 835
L-plug/ GWP□-L	C-plug/ GWP□-C	Y type plug/ GWP□-Y	Cap/ GWC□	Manifold (single/with R)/ GWMF□-□
 Compatible tube O.D. ø 4 6 8 10 12	 Compatible tube O.D. ø 4 6 8 10 12	 Compatible tube O.D. ø 4 6 8 10 12	 Compatible tube O.D. ø 4 6 8 10 12	 Compatible tube O.D. ø 4/6 4/8 6/8 6/10 8/10
·Refer to page: 835	·Refer to page: 835	·Refer to page: 836	·Refer to page: 836	·Refer to page: 836
Manifold (single)/ GWMF□-0	Manifold (double/with R)/ GWMF□-□-W	Manifold (double)/ GWMF□-0-W	Insert ring Made-to-order product	
 Compatible tube O.D. ø 4/6 4/8 6/8 6/10 8/10	 Compatible tube O.D. ø 4/8 6/10 8/12	 Compatible tube O.D. ø 4/8 6/10 8/12	 Compatible tube O.D. ø 4 6 8 10 12	
·Refer to page: 836	·Refer to page: 837	·Refer to page: 837	·Refer to page: 837	

F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain Separ
Mech Press SW
Res press exh valve
SlowStart
Anti-bac/Bac-remove Filt
Film Resist FR
Oil-ProhR
Med Press FR
No Cu/ PTFE FRL
Outdrs FRL
Adapter Joiner Press Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/ other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro Press SW
ContactSW
AirSens
PresSW Cool
Air Flo Sens/Ctrl
WaterRISens
TotAirSys (Total Air)
TotAirSys (Gamma) Gas generator
RefrDry
DesicDry
HiPolymDry
MainFiltr Dischrg etc
Ending