

F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain
Separ
Mech
Press SW
Res press
exh valve
SlowStart
Anti-bac/Bac-
remove Filt
Film
Resist FR
Oil-ProhR
Med
Press FR
No Cu/
PTFE FRL
Outdrs FRL
Adapter
Joiner
Press
Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/
other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro
Press SW
ContactSW
AirSens
PresSW
Cool
Air Flo
Sens/Ctrl
WaterRtSens
TotAirSys
(Total Air)
TotAirSys
(Gamma)
Gas
generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg
etc
Ending

GWJ

Fitting (small size)

Port size M3 to 1/8 (Rc or R)



● Small push-in fittings suitable for various applications

Space saving with smaller body. Dead space of pipe can be decreased dramatically.

Straight							
Single straight/ GWJS□-□		Female straight/ GWJS3-□-M		Bulkhead/ GWJS3-0-X		Straight/ GWJS3-0	
	Compatible Tube O.D. ø		Compatible Tube O.D. ø		Compatible Tube O.D. ø		Compatible Tube O.D. ø
	3.2		3.2		3.2		3.2
	4						
	6						
·Refer to page: 840		·Refer to page: 840		·Refer to page: 840		·Refer to page: 840	
Elbow							
Different diameter straight/ GWJS□-0		Single elbow/ GWJL□-□		Long elbow/ GWJL□-□-L		Elbow/ GWJL3-0	
	Compatible Tube O.D. ø		Compatible Tube O.D. ø		Compatible Tube O.D. ø		Compatible Tube O.D. ø
	3.2, 4		3.2		3.2		3.2
	3.2, 6		4		4		
			6		6		
·Refer to page: 840		·Refer to page: 840		·Refer to page: 841		·Refer to page: 841	
Tee							
Double tee/ GWJT3-□		D tee/ GWJT3-□-D		Tee/ GWJT3-0		Y tee/ GWJY□-0	
	Compatible Tube O.D. ø		Compatible Tube O.D. ø		Compatible Tube O.D. ø		Compatible Tube O.D. ø
	3.2		3.2		3.2		3.2, 3.2
							3.2, 4
·Refer to page: 841		·Refer to page: 841		·Refer to page: 841		·Refer to page: 841	
Plug							
Blanking plug/ GWJP3-B							
	Compatible Tube O.D. ø						
	3.2						
·Refer to page: 842		● Sales unit is 10 pcs./bag.					

● Sales unit is 10 pcs./bag.