

附表1◆支架形状一览表

A 支架形状		固定式		缓冲式		轻量 缓冲式	低背 固定式	专用 固定式
		标准	小型	标准	小型			
符号	抽真空口 向上	A	MA	C	MC	HC		AE
	抽真空口 横向	B	MB	D	MD	HD	HE	BE
	抽真空口 双横向					HDW	HEW	
	直接安装型	E	ME	F				

附表2◆吸盘直径、尺寸-吸盘形状组合表

D 吸盘形状		R	A	RM	S	B	W	E	L	LB	K	P	F	FH	Q
B 吸盘直径	0.7	φ0.7		●											
	1	φ1	●		●										
	1.5	φ1.5		●											
	2	φ2	●		●	●									
	3	φ3	●		●										
	4	φ4	●		●	●			●						
	6	φ6	●			●	●		●	●					
	8	φ8	●			●	●		●	●					
	10	φ10	●		●	●	●		●	●	●	●	●	●	●
	15	φ15	●	●		●	●		●	●		●	●	●	●
	20	φ20	●	●		●	●	●	●	●	●	●	●	●	
	25	φ25	●	●		●	●					●	●	●	●
	30	φ30	●	●		●	●	●	●		●		●	●	
	35	φ35				●									
	40	φ40	●	●			●	●	●		●				
	50	φ50	●	●		●	●	●			●				
	60	φ60	●	●			●								
	70	φ70				●	●								
	80	φ80	●	●			●								
	100	φ100	●	●		●	●								
	150	φ150	●				●								
	200	φ200	●				●								
B 吸盘尺寸	2×4	2×4						●							
	3.5×7	3.5×7						●							
	4×10	4×10						●							
	4×20	4×20						●							
	4×30	4×30						●							
	5×10	5×10						●							
	5×20	5×20						●							
	5×30	5×30						●							
	6×10	6×10						●							
	6×20	6×20						●							
	6×30	6×30						●							
	8×20	8×20						●							
	8×30	8×30						●							

P4
Series

气缸
电磁阀
气动执行器
开关

真空元件

空压阀

空气元件
节流
调速阀

空压辅助元件
接头
辅助阀

消音器
气管

气体发生装置

流体控制元件

电动机
规格
电动机
规格