

体系表

线性导轨卡爪 LSH-HP系列

产品种类		型 号	缸径 (mm)	
HP1系列	双作用型・单作用型 不带橡胶盖 	LSH-A	φ6	
			φ10	
			φ16	
			φ20	
			φ25	
			φ32	
	双作用型・单作用型 带橡胶盖 	LSH-G LSH-F	φ6	
			φ10	
			φ16	
			φ20	
			φ25	
			φ32	
	双作用型 长行程 不带橡胶盖 	LSHL-A	φ10	
			φ16	
			φ20	
			φ25	
	双作用型 长行程 带橡胶盖 	LSHL-G LSHL-F	φ10	
			φ16	
			φ20	
HP2系列	带测长功能 双作用型 不带橡胶盖 	LSHM-A	φ10	
			φ16	
			φ20	
			φ25	
	带测长功能 双作用型 带橡胶盖 	LSHM-G LSHM-F	φ10	
			φ16	
			φ20	
			φ25	

	夹持力 (N)					动作行程 (mm)	开关型号	记载页码
	5	10	50	100	200			
	■					4	F2S	1
		■				6		
			■			10		
			■			14		
				■		22		
	■					4	F3S	11
		■				6	F2H/V	
			■			10	F3H/V	
			■			14	F3PH/V	
				■		22	T2H/V	
		■				8	T3H/V T2H/VR3 T3PH/V	21
			■			12		
			■			18		
				■		22		
		■				8		29
			■			12		
			■			18		
		■				4	—	35
			■			6		
			■			10		
				■		14		
		■				4	—	43
			■			6		
			■			10		
				■		14		

※供给压力0.5MPa、爪长20mm时的夹持力范围

HP1系列	LSH-A
	LSH-F
	LSH-L
	LSH-A
HP2系列	LSH-F
	LSH-M
	LSH-M
	LSH-F
选型	
技术资料	
气缸开关的注意事项	
使用注意事项	
关联产品	