

：不可对应

配管口径栏

○

：Rp

●

：JIS法兰

▲

：DIN法兰

●

：Rp和JIS法兰2种

机种系列名称			使用压力			氢气对应	打开动作		配管口径															记载页码
			低压	中间压力	中压		快	慢	8A	15A		20A	25A	32A	40A	50A	65A	80A	100A	125A	150A	200A	250A	
									1/4	1/2		3/4	1	1 1/4	1 1/2	2	2 1/2	3	4	5	6	8	10	
燃气组合阀	GHV		○	○		○	○	○					◎	◎	◎	◎								3
	GRV		○	○	○	○		○																7
电磁阀	DSG		○			○	○			◎		◎	◎											9
	DSG-W		○			○	○					◎	◎											13
	VNA		○	○		○	○			◎		◎	◎	◎	◎	◎								15
	VLA		○	○		○		○		◎		◎	◎	◎	◎	◎								21
	VNA-R/RH		○	○	○	○	○					◎	◎	◎	◎									25
	VNR		○	○		○	○				◎		◎	◎	◎									
中压燃气安全截止控制系统	TAC-25				○		○	○					● IN侧		● OUT侧									31
	VNM		○	○	○	○	○						●											35
	VLM		○	○	○	○		○					●											37
	C25N-B				○								● IN侧		● OUT侧									39
安全截止阀	VNM-25-K		○	○	○		○						●											41
液动阀	HK1		○	○	○	○		○						●	●	●	●	▲	▲	▲	▲			43
	HS		○	○	○	○		○							●		●							47