


体系表

紧凑型气缸 SSG系列

●：标准、◎：准标准、■：不可制作

种类	型号 JIS符号	缸径 (mm)	行程 (mm)												最大行程 (mm)	最小行程 (mm)	开关	记载页码
			5	10	15	20	25	30	35	40	45	50	75	100				
双作用·单活塞杆型 带开关 带双色显示、断电延迟型、 T1开关	SSG SSG-L SSG-L1 	φ12·φ16	●	●	●	●	●	●							30	1	◎	1068
		φ20·φ25	●	●	●	●	●	●	●	●	●				50			
		φ32·φ40	●	●	●	●	●	●	●	●	●	●	●	●	100			
		φ50·φ63·φ80·φ100	■	●	●	●	●	●	●	●	●	●	●	●				

SCP※3

CMK2

CMA2

SCM

SCG

SCA2

SCS2

CKV2

CAV2·
COVP/N2

SSD2

SSG

SSD

CAT

MDC2

MVC

SMG

MSD·
MSDG

FC※

STK

SRL3

SRG3

SRM3

SRT3

MRL2

MRG2

SM-25

缓冲器

FJ

FK

调速阀

卷末