

●：标准、◎：准标准、■：不可制作

种类	型号	缸径 (mm)	标准行程 (mm)									最小行程 (mm)	最大行程 (mm)	选择项			开关	记载页码	
														两侧带全行程调整部件	R侧带全行程调整部件	L侧带全行程调整部件			
		50	100	150	200	300	400	500	600	700	A	A1	A2						
双作用型	MRG2 	φ10	●	●	●	●	●					50	300				◎	1766	
		φ16	●	●	●	●	●	●						500	◎	◎			◎
		φ25	●	●	●	●	●	●	●	●	●			700					

SCP※3
CMK2
CMA2
SCM
SCG
SCA2
SCS2
CKV2
CAV2・COVP/N2
SSD2
SSG
SSD
CAT
MDC2
MVC
SMG
MSD・MSDG
FC※
STK
SRL3
SRG3
SRM3
SRT3
MRL2
MRG2
SM-25
缓冲器
FJ
FK
调速阀
卷末