

体系表

倍力气缸 SHC系列

LCM
LCR
LCG
LCW
LCX
STM
STG
STS・STL
STR2
UCA2
ULK※
JSK/M2
JSG
JSC3・JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3※
NHS
HRL
LN
卡爪
卡盘
机械卡爪・卡盘
缓冲器
FJ
FK
速度控制器
卷末

种类	型号 JIS符号	缸径 (mm)	标准行程 (mm)													最小行程 (mm)	最大行程 (mm)	中间行程 (每mm)	增力行程 (mm)	安装形式		
																				基本型	轴向脚座型	
			100	150	200	250	300	350	400	500	600	700	800	900	1000					10	20	00
双作用・2倍力型	SHC	φ40・φ50	●	●	●	●	●	●	●	●	●				40	700	5	●	●	●	●	
		φ63	●	●	●	●	●	●	●	●	●	●				800		●	●	●	●	
		φ80	●	●	●	●	●	●	●	●	●	●	●			900		●	●	●	●	
		φ100	●	●	●	●	●	●	●	●	●	●	●	●		1000		●	●	●	●	
双作用・4倍力型	SHC-K	φ40・φ50	●	●	●	●	●	●	●	●	●				40	700	5	●	●		●	
		φ63	●	●	●	●	●	●	●	●	●	●				800		●	●		●	
		φ80	●	●	●	●	●	●	●	●	●	●	●			900		●	●		●	
		φ100	●	●	●	●	●	●	●	●	●	●	●	●		1000		●	●		●	

●：标准 ○：准标准 ○：接单生产 ■：不可制作

安装形式								缓冲		选择项												附件								开关	记载页码
	前端法兰型	后端法兰型	单耳环型	双耳环型	中间耳轴型	前端耳轴型	后端耳轴型	不带缓冲	后端缓冲	杆端形状外螺纹	杆端形状法兰	配管口		位置		防尘套(100℃)	防尘套(250℃)	金属刮板	防紫色化	增力部单独控制用气口	单耳环连接件	双耳环连接件	单耳环支撑件(耳环用)	双耳环支撑件(耳环用)	单耳环支撑件(连接件用)	双耳环支撑件(连接件用)					
	FA	FB	CA	CB	TC	TA	TB	N	H	无符号	F	无符号	R	S	T	J	L	G1	P6	A	I	Y	B11	B21	B12	B22					
	●	●	●	●	●	●	●	●	●	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	1144		
	●	●	●	●	●	●	●	●	●	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	1144		
	●	●	●	●	●	●	●	●	●	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	1144		
	●	●	●	●	●	●	●	●	●	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	1144		
	●					●		●	●	○	○	○	○	○	○	○	○	○	○	○	○	○			○	○		1154			
	●					●		●	●	○	○	○	○	○	○	○	○	○	○	○	○	○			○	○		1154			
	●					●		●	●	○	○	○	○	○	○	○	○	○	○	○	○	○			○	○		1154			
	●					●		●	●	○	○	○	○	○	○	○	○	○	○	○	○	○			○	○		1154			

LCM
LCR
LCG
LCW
LCX
STM
STG
STS-STL
STR2
UCA2
ULK※
JSK/M2
JSG
JSC3・JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3※
NHS
HRL
LN
卡爪
卡盘
机械卡爪・卡盘
缓冲器
FJ
FK
速度控制器
卷末