

● 气缸阀

分类		机种名称	通口数	动作方式						
				NC	NO	双作用	Rc1/4	Rc3/8	Rc1/2	
气 缸 阀	气控型 	水・液体用 SAB※W	2 通	●	●	●	●	●	●	
		空气・燃气用 SAB※A		●	●	●	●	●	●	
		低真空用 SAB※V		●	●	●	●	●	●	
		蒸汽・水・空气用 SAB※S		●	●	●	●	●	●	
	电磁阀搭载型 	水・液体用 SVB※W		●	●		●	●	●	
		空气・燃气用 SVB※A		●	●		●	●	●	
		低真空用 SVB※V		●	●		●	●	●	
		蒸汽・水・空气用 SVB※S		●	●		●	●	●	
小型气 缸 阀	气控型 	通用 NAB※	●	●	●	●	●			
		低真空用 NAB※V	●	●	●	●	●			
	气控型 集成式 	通用 GNAB※	●	●	●	A口 ●	C口 ●			
		低真空用 GNAB※V	●	●	●	A口 ●	C口 ●			

● 隔膜式气缸阀

系列	机种型号	使用压力		动作方式			通径				
		低真空	正压	NC	NO	双作用	φ7	φ8	φ12	φ20	
	LAD※-10A		●	●	●	●		●			
	LAD※-15A		●	●	●	●			●		
	LAD※-20A		●	●	●	●				●	
	LAD※-25A		●	●	●	●				●	
	NAD※-10		●	●	●	●	●				
	NAD※V-10	●	●	●	●	●	●				
	GNAD※-10		●	●	●	●	●				
	GNAD※V-10	●	●	●	●	●	●				

SAB · SVB · NAB · LAD · NAD Series

系列体系表

※内螺纹型还支持G螺纹、NPT螺纹。但，小型气缸阀为接单生产品。

配管口径											记载页码
	Rc3/4	Rc1	Rc1 1/4	32 法兰	Rc1 1/2	40 法兰	Rc2	50 法兰	65 法兰	80 法兰	
	●	●	●	●	●	●	●	●	●	●	506
	●	●	●	●	●	●	●	●	●	●	510
	●	●	●	●	●	●	●	●			514
	●	●	●	●	●	●	●	●			518
	●	●	●	●	●	●	●	●	●	●	522
	●	●	●	●	●	●	●	●	●	●	530
	●	●	●	●	●	●	●	●			534
	●	●	●	●	●	●	●	●			538
											544
											544
											548
											548

	配管口径					隔膜材质		阀体材质				底板		记载 页码
	Rc1/4	Rc3/8	Rc1/2	Rc3/4	Rc1	EPDM	PTFE	PPS	SCS13	SUS303	PP	SUS303	A6063	
		●				●	●	●	●					556
			●			●	●	●	●					
				●		●	●	●	●					
					●	●	●	●	●					
		●				●			●					560
		●				●			●					
	A口 ●	C口●				●				●	●	●	●	562
	A口 ●	C口●				●				●	●	●	●	

注：G螺纹、NPT螺纹为接单生产品。请咨询本公司。

EXA
FWD
HNB/G
USB/G
FAB/G
FGB/G
FVB
FWB/G
FHB
FLB
AB
AG
AP·AD
APK·ADK
干燥
空气用
EX防爆型
防爆型
HVB·HVL
S◇B·NAB
LAD·NAD
水用
相关
NP·NAP·NVP
SNP
CHB/G
MXB/G
其他阀
SWD·MWD
集尘用
CVE·CVSE
CCH·CPE/D
生命
科学
燃气
自动
洒水
室外
专用
特殊
流体
接单
生产品
卷末