

			机种名称	通口数	材质		流体				
					密封件	阀体	纯水	生理盐水	试剂	废液	清洗剂
电 磁 阀	无金属	膜片型	MR10R	2・3	FKM	PEEK	●	●	●	●	●
			MR16	2・3	FKM EPDM	PEEK	●	●	●	●	●
			MKB3	2	FKM EPDM	PPS	●	●	●	●	●
			MAB1	2	PTFE	PTFE	●	●	●	●	●
			MAG1	3	PTFE	PTFE	●	●	●	●	●
			MYB1	2	FKM	PPS	●	●	●	●	●
			MYG1	3	FKM	PPS	●	●	●	●	●
			MYB2	2	FKM	PPS	●	●	●	●	●
			MYG2	3	FKM	PPS	●	●	●	●	●
			MYB3	2	FKM	PPS	●	●	●	●	●
			MYG3	3	FKM	PPS	●	●	●	●	●
			MEB2	2	PTFE FFKM	PPS	●	●	●	●	●
			MEG2	3	PTFE FFKM	PPS	●	●	●	●	●
			MJB3	2	FKM	PPS PSU	●	●	●	●	●
			EMB21	2	PTFE	SUS316 PTFE	● ●	●	●	●	●
			EMB41・51	2	PTFE	PTFE	●	●	●	●	●
		杆型	HMTB1	2	NBR FKM	PPS	●	●	●	●	●
			HMTG1	3	EPDM		●	●	●	●	●
	高耐腐蚀	截止型	USB2・3	2	NBR FKM	PPS	●	●	●	●	●
			USG2・3	3	NBR FKM	PPS	●	●	●	●	●
			UMB1	2	FKM	SUS304相当	●	●	●	●	●
			UMG1	3	FKM	SUS304相当	●	●	●	●	●
			HB	2	NBR FKM PTFE	SUS316	●	●	●	●	●
			USB2・3	2	NBR (FKM)	C3604 SUS304	●	●	●	●	●
			USG2・3	3	NBR (FKM)	C3604 SUS304	●	●	●	●	●
管夹阀	无金属型		HYN	2・3	-	-	●	●	●	●	●

注：关于流体，请在确认密封件・阀体材质的基础上选择阀。

通径(mm)																				记载页码
	0.5	0.9	1	1.2	1.5	1.6	1.8	2	2.3	3	3.2	4	5	6	7	8	10	12	15	
			●																	10
						●														15
					●															21
						● 1.6 相当														25
						● 1.6 相当														25
								● 2.0 相当												28
								● 2.0 相当												28
										● 3.0 相当										31
										● 3.0 相当										31
													● 5.0 相当							35
													● 5.0 相当							35
										● 3.0 相当										38
										● 3.0 相当										38
										●										41
										●										43
														●		●	●	●	●	45
						●														49
						●														49
			●			●			●											53
			●		●	●														53
		●																		57
		●																		57
			●		●	●			●	●	●	●			●					59
			●	●	●	●	●		●		●									63
			●	●	●		●	●												67
			● 管径							● 管径				● 管径						71