



中国国家强制性产品认证证书



证书编号: 2020322316000978

认证委托人名称: G. M. INTERNATIONAL S. R. L.
 认证委托人地址: Via Mauro Macchi 27, I-20124 Milano (MI) Italy
 生产者名称: G. M. INTERNATIONAL S. R. L.
 生产者地址: Via Mauro Macchi 27, I-20124 Milano (MI) Italy
 生产企业名称: G. M. INTERNATIONAL S. R. L.
 生产企业地址: Via G. Mameli 53/55 I-20852 Villasanta (MB) Italy

产品名称: 隔离式安全栅/电源/隔离器
 系列、规格、型号: D5000 系列
 标准: GB 3836.1-2010、GB 3836.4-2010、GB 3836.8-2014、
 GB 12476.1-2013、GB 12476.4-2010

上述产品符合强制性产品认证实施规则 CNCA-C23-01:2019 的要求, 特发此证。

发证日期: 2020 年 9 月 20 日 有效期至: 2025 年 9 月 1 日

首次发证日期: 2020 年 9 月 2 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询



批准:



上海仪器仪表自控系统检验测试所有限公司

<http://www.sitiias.com.cn>

中国·上海·漕宝路103号200233

电话: +86 21 64510844

S 0001884



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION



CERTIFICATE NO: 2020322316000978

APPLICANT: G.M. INTERNATIONAL S.R.L.
ADDRESS: Via Mauro Macchi 27, I-20124 Milano (MI) Italy
MANUFACTURER: G.M. INTERNATIONAL S.R.L.
ADDRESS: Via Mauro Macchi 27, I-20124 Milano (MI) Italy
FACTORY: G.M. INTERNATIONAL S.R.L.
ADDRESS: Via G. Mameli 53/55 I-20852 Villasanta (MB) Italy

PRODUCTNAME: Isolated safety Barrier/Power supply/Isolator
SERIES,SPECIFICATION,MODEL: D5000 Series
STANDARDS: GB 3836.1-2010、GB 3836.4-2010、GB 3836.8-2014、
 GB 12476.1-2013、GB 12476.4-2010

This is to certify that the above mentioned product(s)complies with the requirements of implementation rules for compulsory certification (REFNO. CNCA-C23-01:2019).

Valid from:September 20, 2020

Valid until: September 1, 2025

Date of original certification:September 2, 2020

The validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

This certificate is available through CNCA's website: www.cnca.gov.cn



APPROVAL:

Xu JianPing



Shanghai Inspection and Testing Institute of Instruments and Automation Systems Co., Ltd.

<http://www.sitiias.com.cn>

Building 9,103 Cao Bao Road, Shanghai 200233,China

Tel: +86 21 64510844



中国国家强制性产品认证证书



SITIAs
Worldwide Access

证书编号: 2020322316000978

附件

型号规格:

D5032S, D5032S-xxx, D5032D, D5032D-xxx

D5034S, D5034S-xxx, D5034D, D5034D-xxx

D5036S, D5036S-xxx, D5036D, D5036D-xxx

D5037S, D5037S-xxx, D5037D, D5037D-xxx

D5038S*, D5038S*-xxx, D5038D*, D5038*-xxx, D5038X*, D5038X*-xxx

D5039S*, D5039S*-xxx, D5039D*, D5039*-xxx, D5039X*, D5039X*-xxx

注*: 输出电阻, 代码为任意一位字符。

D5231E, D5231E-xxx

Digital output:

D5040S, D5040S-xxx, D5040D, D5040D-xxx

D5048S, D5048S-xxx

批准:



上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书



SITIAs
Worldwide Access

证书编号: 2020322316000978

附件

电气参数:

	最高输入电压 U_i (V)	最大输入电流 I_i (mA)	最大输入功率 P_i (W)
	--	--	--
	内部等效参数		
	C_i (μF)	L_i (mH)	
	--	--	

型号	端子 代码	最高输出电压 U_o (V)	最大输出电流 I_o (mA)	最大输出功率 P_o (mW)
D5048S, D5048S-xxx D5049S, D5049S-xxx	9-10	24.8	93	571
		气体组别	最大外部参数	
			C_o (nF)	L_o (mH)
		II C	113	4.19
		II B / Ia D	860	16.79
		II A	3050	33.58
		最高输入电压 U_i (V)	最大输入电流 I_i (mA)	最大输入功率 P_i (W)
		--	--	--
内部等效参数				
		C_i (μF)	L_i (mH)	
		--	--	

型号: D5072S, D5072S-xxx, D5072S-087, D5072D, D5072D-xxx

型号	电源工作参数	
	U_n (V d.c. / V a.c.)	P_n (W)
D5072S, D5072S-xxx	24	≤ 1
D5072S-087	24	≤ 0.8
D5072D, D5072D-xxx	24	≤ 1.5

批准:



上海仪器仪表自控系统检验测试所有限公司