


Full stroke adjusting bracket kit

- Both-side full stroke adjusting bracket kit


SRG3 - 25 - A

Bore size
(Item (B) on page 1652)

[ø12 to ø20]



[ø25]



No.	Part name	Quantity
1	Hexagon socket head cap screw	ø12 to ø20:2 ø25:-
2	Hexagon socket head cap screw	4
3	Plastic bag	1
4	Package label	1
5	Shock absorber	2
6	Hexagon socket set screw	2
7	Flat nut	2
8	Adaptor nut	2
9	Hexagon nut	2
10	ø12 to ø20: Plate (R) ø25: Plate	ø12 to ø20:1 ø25:2
11	Plate (L)	ø12 to ø20:1 ø25:-
12	Hexagon nut	2
13	Hexagon socket head cap screw	ø12 to ø20:6 ø25:8
14	Adaptor (RG)	1
15	Adaptor (LG)	1
16	Hexagon socket head cap screw	ø12 to ø20:6 ø25:4
17	Adaptor (R)	1
18	Adaptor (L)	1

SCP*3

CMK2

CMA2

SCM

SCG

SCA2

SCS2

CKV2

CAV2/
COVP/IN2

SSD2

SSG

SSD

CAT

MDC2

MVC

SMG

MSD/
MSDG

FC*

STK

SRL3

SRG3

SRM3

SRT3

MRL2

MRG2

SM-25

ShkAbs

FJ

FK

Spd
Contr

Ending


Full stroke adjusting bracket kit

● R side full stroke adjusting bracket kit


SRG3 - 25 - A1

Bore size
(Item ⑧ on page 1652)

[ø12 to ø20]



[ø25]



No.	Part name	Quantity
1	Hexagon socket head cap screw	ø12 to ø20:1 ø25:-
2	Hexagon socket head cap screw	2
3	Plastic bag	1
4	Package label	1
5	Shock absorber	1
6	Hexagon socket set screw	1
7	Flat nut	1
8	Adaptor nut	1


No.	Part name	Quantity
9	Hexagon nut	1
10	ø12 to ø20: Plate (R) ø25: Plate	1
11	Hexagon nut	1
12	Hexagon socket head cap screw	ø12 to ø20:3 ø25:4
13	Adaptor (RG)	1
14	Hexagon socket head cap screw	ø12 to ø20:3 ø25:2
15	Adaptor (L)	1

● L side full stroke adjusting bracket kit


SRG3 - 25 - A2

Bore size
(Item ⑧ on page 1652)

[ø12 to ø20]



[ø25]



No.	Part name	Quantity
1	Hexagon socket head cap screw	ø12 to ø20:1 ø25:-
2	Hexagon socket head cap screw	2
3	Plastic bag	1
4	Package label	1
5	Shock absorber	1
6	Hexagon socket set screw	1
7	Flat nut	1
8	Adaptor nut	1

No.	Part name	Quantity
9	Hexagon nut	1
10	ø12 to ø20: Plate (L) ø25: Plate	1
11	Hexagon nut	1
12	Hexagon socket head cap screw	ø12 to ø20:3 ø25:4
13	Adaptor (LG)	1
14	Hexagon socket head cap screw	ø12 to ø20:3 ø25:2
15	Adaptor (R)	1

Parts kit weight list

Full stroke adjusting kit

- Both side full stroke adjusting bracket kit

Kit No.	Kit weight (g)
SRG3-12-A	244
SRG3-16-A	261
SRG3-20-A	405
SRG3-25-A	813

- R side full stroke adjusting bracket kit

Kit No.	Kit weight (g)
SRG3-12-A1	122
SRG3-16-A1	131
SRG3-20-A1	202
SRG3-25-A1	406

- L side full stroke adjusting bracket kit

Kit No.	Kit weight (g)
SRG3-12-A2	122
SRG3-16-A2	130
SRG3-20-A2	403
SRG3-25-A2	407

The other parts kits are the same as those of SRL3 Series.
Refer to SRL3 Series on pages 1627 and 1628.

SCP*3
CMK2
CMA2
SCM
SCG
SCA2
SCS2
CKV2
CAV2/ COVP/IN2
SSD2
SSG
SSD
CAT
MDC2
MVC
SMG
MSD/ MSDG
FC*
STK
SRL3
SRG3
SRM3
SRT3
MRL2
MRG2
SM-25
ShkAbs
FJ
FK
Spd Contr
Ending