

Included component

Bracket Outdoor Series

BW Series


Joiner Outdoor Series

JW Series



Dimensions


T-bracket set



Material: Aluminum die-casting
Stainless steel mounting screws used


Model No.	Compatibility	A	B	C	D	E	F	G	H	I	J	K	kg
BW310-W	3000 Series FXW1004 Series	60	45	10	125	7	14	22	27	7	JIS B2401-P21	45	0.086
BW410-W	4000 Series FXW1011 Series	60	45	10	125	7	14	22	37	7	JIS B2401-P21	55	0.094
BW810-W	8000 Series FXW1037 Series	70	50	15	150	9	14	27	37	8	AS568-127	65	0.169

Joiner set



Material: Aluminum die-casting
Stainless steel mounting screws used

Model No.	Compatibility	A	B	C	D	E	kg
C4000-JW400-W	3000 Series 4000 Series FXW1004 Series FXW1011 Series	21	44	32	M5	JIS B2401-P21	0.036
C8000-JW800-W	8000 Series FXW1037 Series	26	65	50	M6	AS568-127	0.094



Pipe adaptor Outdoor Series


AW400, AW800 Series

Port size: Rc1/4 to Rc11/4



Dimensions


Pipe adaptor set



Material: Aluminum die-casting
Stainless steel mounting screws used

Model No.	Port size	Compatibility	A	B	C	D	E (O-ring)	F (gasket)	Other
AW400-8-W	Rc ¹ / ₄	3000 Series 4000 Series FXW1004 Series FXW1011 Series	20 (25) [34]	6 (11) [20]	50	45	JISB2401 P21 1 pc.	1 pc.	Values in () are for Rc ³ / ₄ Values in [] are for the Rc1
AW400-10-W	Rc ³ / ₈								
AW400-15-W	Rc ¹ / ₂								
AW400-20-W	Rc ³ / ₄								
AW400-25-W	Rc1	8000 Series FXW1037 Series	35 (38)	15 (18)	81	66	AS568-127 1 pc.	1 pc.	Values in () are for Rc1 ¹ / ₄
AW800-20-W	Rc ³ / ₄								
AW800-25-W	Rc1								
AW800-32-W	Rc1 ¹ / ₄								

Pipe adaptor set



Material: Aluminum die-casting
Stainless steel mounting screws used

Model No.	Port size	Compatibility	A	B	C	D	E (O-ring)	F (gasket)	Other
AW400-8-W-B31W	Rc ¹ / ₄	3000 Series FXW1004 Series	20	6	50	45	JISB2401 P21 1 pc.	1 pc.	-
AW400-10-W-B31W	Rc ³ / ₈								
AW400-15-W-B31W	Rc ¹ / ₂								
AW400-8-W-B41W	Rc ¹ / ₄	3000 Series 4000 Series FXW1004 Series FXW1011 Series	20 (25) [34]	6 (11) [20]	50	45	JISB2401 P21 1 pc.	1 pc.	Values in () are for Rc ³ / ₄ Values in [] are for the Rc1
AW400-10-W-B41W	Rc ³ / ₈								
AW400-15-W-B41W	Rc ¹ / ₂								
AW400-20-W-B41W	Rc ³ / ₄								
AW400-25-W-B41W	Rc1	8000 Series FXW1037 Series	35 (38)	15 (18)	81	66	AS568-127 1 pc.	1 pc.	Values in () are for Rc1 ¹ / ₄
AW800-20-W-B81W	Rc ³ / ₄								
AW800-25-W-B81W	Rc1								
AW800-32-W-B81W	Rc1 ¹ / ₄								