







# Series variation



## Linear slide cylinder LCX Series

- LCM
- LCR
- LCG
- LCW
- LCX**
- STM
- STG
- STS/STL
- STR2
- UCA2
- ULK\*
- JSK/M2
- JSG
- JSC3/JSC4
- USSD
- UFCD
- USC
- UB
- JSB3
- LMB
- LML
- HCM
- HCA
- LBC
- CAC4
- UCAC2
- CAC-N
- UCAC-N
- RCS2
- RCC2
- PCC
- SHC
- MCP
- GLC
- MFC
- BBS
- RRC
- GRC
- RV3\*
- NHS
- HRL
- LN
- Hand
- Chuk
- MechHnd/Chuk
- ShkAbs
- FJ
- FK
- SpdContr
- Ending

Variation	Model No.  JIS symbol	Bore size  (mm)	Stroke length (mm)										
			10	20	30	40	50	75	100	125	150		
Double acting/single rod	LCX 	ø25/ø32	●	●	●	●	●						
Double acting/position locking	LCX-Q 	ø25/ø32	●	●	●	●	●						
Double acting/single rod clean-room specifications	LCX-P7* 	ø25/ø32	●	●	●	●	●						
Double acting/single rod long stroke length	LCX-*L 	ø25/ø32							●	●	●	●	
Double acting/position locking long stroke length	LCX-Q-*L 	ø25/ø32							●	●	●	●	
Double acting/single rod clean-room specifications long stroke length	LCX-*L-P7* 	ø25/ø32							●	●	●	●	

●: Standard ○: Option ○: Made to order ■: Not available

	Option																		With positioning hole	Center stopper	Switch	Page	
	Cushion stopper						Metal stopper						Shock absorber stopper										
	Stopper position ①	Stopper position ②	Stopper position ③	Stopper position ④	Stopper position ①/③	Stopper position ②/④	Stopper position ①	Stopper position ②	Stopper position ③	Stopper position ④	Stopper position ①/③	Stopper position ②/④	Stopper position ①	Stopper position ②	Stopper position ③	Stopper position ④	Stopper position ①/③	Stopper position ②/④					
	S1	S2	S3	S4	S5	S6	M1	M2	M3	M4	M5	M6	A1	A2	A3	A4	A5	A6	E	*1			
	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	254
	○	○	■	■	■	■	○	○	■	■	■	■	○	○	■	■	■	■	○	○	○	○	264
	○	○	○	○	○	○	○	○	○	○	○	○	■	■	■	■	■	■	○	○	○	○	270
	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	●	○	○	○	276
	○	○	■	■	■	■	○	○	■	■	■	■	○	○	■	■	■	■	○	○	○	○	286
	○	○	○	○	○	○	○	○	○	○	○	○	■	■	■	■	■	■	○	○	○	○	292

\*1: The center stopper is a made-to-order product. Contact CKD for details.

● Stopper position

