













ZSP












Fitting stainless steel

Port size: M5, R1/8 to R1/2



Straight ZSP-C□-□		Union straight ZSP-U□		Elbow ZSP-L□-□	
	Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø
	4		4		4
	6		6		6
	8		8		8
	10		10		10
	12		12		12
·Refer to page: 851		·Refer to page: 851		·Refer to page: 851	
Union elbow ZSP-V□		Tee ZSP-B□-□		Union tee ZSP-E□	
	Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø
	4		4		4
	6		6		6
	8		8		8
	10		10		10
	12		12		12
·Refer to page: 851		·Refer to page: 852		·Refer to page: 852	
Different diameter union straight ZSP-G□-□		Branch tee ZSP-D□-□		Tripod elbow ZSP-VX□-□	
	Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø
	6/4		4		4
	8/6		6		6
	10/8		8		8
	12/10		10		10
			12		12
·Refer to page: 852		·Refer to page: 852		·Refer to page: 853	
Union Y ZSP-Y□		Different diameter union tee ZSP-EG□-□		Branch Y ZSP-X□-□	
	Compatible tube O.D. ø		Compatible tube O.D. ø		Compatible tube O.D. ø
	4		6/4		4
	6		8/6		6
	8		10/8		8
	10		12/10		10
	12				12
·Refer to page: 853		·Refer to page: 853		·Refer to page: 853	

· Sales unit is 10 pcs./bag.

Branch double Y ZSP-RX□-□		Compatible tube O.D. Ø 4 6	Different diameter double Y ZSP-RG□-□		Compatible tube O.D. Ø 6/4 8/6	Tripod union ZSP-VU□		Compatible tube O.D. Ø 4 6 8 10 12
·Refer to page: 854			·Refer to page: 854			·Refer to page: 854		
Different diameter union Y ZSP-W□-□		Compatible tube O.D. Ø 6/4 8/6 10/8 12/10	Union A ZSP-AU□		Compatible tube O.D. Ø 4 6 8 10 12	Branch elbow ZSP-AX□-□		Compatible tube O.D. Ø 4 6 8 10 12
·Refer to page: 854			·Refer to page: 855			·Refer to page: 855		
Branch triple ZSP-KD□-□-□		Compatible tube O.D. Ø 6/4 8/4 8/6 10/8	Different diameter triple ZSP-KG□-□		Compatible tube O.D. Ø 6/4 8/4 8/6 10/6 10/8	Cap ZSP-PF□		Compatible tube O.D. Ø 4 6 8 10 12
·Refer to page: 855			·Refer to page: 855			·Refer to page: 856		
Bulkhead union ZSP-M□		Compatible tube O.D. Ø 4 6 8 10 12	Reducer ZSP-J□-□		Compatible tube O.D. Ø 6/4 4/6 4/8 6/8 4/10 6/10 8/10 6/12 8/12 10/12			
·Refer to page: 856			·Refer to page: 856					

· Sales unit is 10 pcs./bag.

F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain
Separ
Mech
Press SW
Res press
exh valve
SlowStart
Anti-bac/Bac-
remove Filtr
Film
Resist FR
Oil-ProhR
Med
Press FR
No Cu/
PTFE FRL
Outdrs FRL
Adapter
Joiner
Press
Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/
other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro
Press SW
ContactSW
AirSens
PresSW
Cool
Air Flo
Sens/Ctrl
WaterRISens
TotAirSys
(Total Air)
TotAirSys
(Gamma)
Gas
generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg
etc
Ending