

体系表

ライフサイエンス機器

	機種名	ポート数	材質		流体						
			シール	ボディ	純水	生理食塩水	試薬	廃液	洗浄液		
電 磁 弁	メタルフリー ダイアフラムタイプ	MR10R	2・3	FKM	PEEK	●	●	●	●	●	
		MR16	2・3	FKM EPDM	PEEK	●	●	●	●	●	
		MKB3	2	FKM EPDM	PPS	●	●	●	●	●	
		MAB1	2	PTFE	PTFE	●	●	●	●	●	
		MAG1	3	PTFE	PTFE	●	●	●	●	●	
		MYB1	2	FKM	PPS	●	●	●	●	●	
		MYG1	3	FKM	PPS	●	●	●	●	●	
		MYB2	2	FKM	PPS	●	●	●	●	●	
		MYG2	3	FKM	PPS	●	●	●	●	●	
		MYB3	2	FKM	PPS	●	●	●	●	●	
		MYG3	3	FKM	PPS	●	●	●	●	●	
		MEB2	2	PTFE FFKM	PPS	●	●	●	●	●	
		MEG2	3	PTFE FFKM	PPS	●	●	●	●	●	
		MJB3	2	FKM	PPS PSU	●	●	●	●	●	
		EMB21	2	PTFE	SUS316 PTFE	●	●	●	●	●	
	EMB41・51	2	PTFE	PTFE	●	●	●	●	●		
	タレ イバ プー	HMTB1	2	NBR FKM	PPS	●	●	●		●	
		HMTG1	3	EPDM		●	●	●		●	
	高耐 食	ポベ ット タイプ	USB2・3	2	NBR FKM	PPS	●				
			USG2・3	3	NBR FKM	PPS	●				
UMB1			2	FKM	SUS304相当	●					
UMG1			3	FKM	SUS304相当	●					
HB			2	NBR FKM PTFE	SUS316	●					
USB2・3			2	NBR (FKM)	C3604 SUS304						
USG2・3			3	NBR (FKM)	C3604 SUS304						
バビ ル プ チ	メタルフリー タイプ	HYN	2・3	-	-	●	●	●	●	●	

注：流体については、シール・ボディ材質をご確認の上バルブを選定ください。

オリフィス径(mm)																				記載ページ
0.5	0.9	1	1.2	1.5	1.6	1.8	2	2.3	3	3.2	4	5	6	7	8	10	12	15		
		●																		10
					●															15
				●																21
					● 1.6 相当															25
					● 1.6 相当															25
							● 2.0 相当													28
							● 2.0 相当													28
									● 3.0 相当											31
									● 3.0 相当											31
													● 5.0 相当							35
													● 5.0 相当							35
									● 3.0 相当											38
									● 3.0 相当											38
									●											41
									●											43
													●		●	●	●	●		45
					●															49
					●															49
		●			●			●												53
		●		●	●															53
	●																			57
	●																			57
		●		●	●			●	●	●	●				●					59
		●	●	●	●	●		●		●										63
		●	●	●		●	●													67
		● チューブ 内径							● チューブ 内径				● チューブ 内径							71