



Oil mist filter Standard White Series

M1000/M2000/M3000

M4000/M6000/M8000-W Series

Ideal for circuits susceptible to oil, including measuring, and instrumentation circuits.

● Port size: 1/8 to 1

JIS symbol 

RoHS

CAD

Specifications

Item	M1000-W	M2000-W	M3000-W	M4000-W	M6000-W	M8000-W
Appearance						
Working fluid	Compressed air					
Working pressure MPa	0.1 (≈15 psi, 1 bar) to 1.0 (≈150 psi, 10 bar) *2, *3					
Proof pressure MPa	1.5 (≈220 psi, 15 bar) *2					
Drain capacity cm ³	3	25	45	80	80	80
Port size Rc,NPT,G	1/8,1/4 (3/8 uses an adaptor)	1/4,3/8 (1/2 uses an adaptor)		1/4,3/8,1/2 (3/4 uses an adaptor)	3/4,1 (1 1/4 uses an adaptor)	3/4,1 (1 1/4 uses an adaptor)
Weight kg	0.096	0.25	0.28	0.52	0.95	1.35
Standard accessories	Bowl guard					

Mantle option name		Blank (M type)	S (S type)	X (X type)
Max. processing flow rate ℓ /min(ANR) Primary pressure 0.7 MPa	M1000-□-W	150 *2	150 *2	150
	M2000-□-W	250	310	310
	M3000-□-W	360	450	450
	M4000-□-W	825	1000	1000
Ambient / fluid temperatures °C	M6000-□-W	1270	1400	1400
	M8000-□-W	2600	2900	2900
Filtration rating μm	0.01 (nominal)		0.3	Suction by activated charcoal
Secondary side oil concentration mg/m ³	≤0.01 (≤0.1 after oil saturation) *4, 5		0.5 or less *4	0.003 or less *6
Mantle (element) change	1 year (6000 hours) or pressure drop 0.1 MPa		- *7	

- *1: Use within the max. processing flow rate.
If the max. processing flow rate is exceeded temporarily, or if the filter is installed at a location with high levels of pulsation, the mantle could be damaged or oil or drainage, etc., could splatter to the secondary side and result in a terminal malfunction.
- *2: When using M1000-W-F1 auto-drain, the min. working pressure is 0.2 MPa, the max. working pressure is 0.7 MPa and the proof pressure is 1.05 MPa. For the max. processing flow rate, refer to the max. processing flow rate graph (page 119).
- *3: In the case of "F1" with auto-drain, the min. working pressure is 0.15 MPa.
- *4: The secondary oil concentration is the value when the primary oil concentration is 30 mg/m³ and inlet air temperature is 21°C.
- *5: Install an oil mist filter (S type) as a pre-filter on the primary side to prevent early clogging.
- *6: When an oil mist filter (M Series M type) is installed on the primary side.
- *7: The mantle (element) replacement period differs depending on the odor density in compressed air, and thus cannot be clearly indicated.
Consider the total period from initial installation to when the smell of oil is confirmed as the effective deodorizing period, and replace at the same time as the M type or control with usage time. (When the inlet temperature is 21°C, replace at the control time or 1,000 hours, whichever is sooner)
Keep the primary air temperature at 30°C or less. The deodorizing effect will drop if temperature is high, so provide heat dissipation measures.

Differential pressure switch/Switch specifications


Differential pressure switch option name	Differential pressure switch option Q3/Q4	
	Reed 2-wire	
Load voltage	12/24 VDC	110 VAC
Load current *1	5 to 50 mA	7 to 20 mA
Internal voltage drop	3 V or less	
Display lamp	Red LED (Lit when ON)	
Lead wire length	3 m (oil resistant vinyl cabtyre cable 2-conductor 0.2 mm ²)	
Impact resistance	294 m/s ²	
Insulation resistance	20 MΩ and over with 500 VDC megger	
Withstand voltage	No failure after 1 minute of 1,000 VAC application	
Degree of protection	IEC Standard IP67, JIS C0920 (water-tight), oil resistance	
Contact protection circuit	None	

*1: Install a load resistor before use.

CE marking specifications

Compatible as standard.

Switch internal circuit diagram



Option weight

* Add to the weight of the standard accessories.

Unit: kg

Code	Drain discharge	Bowl material		Differential pressure indicator		Differential pressure switch		Pipe adaptor set							Bracke
	F1	M	M1	Q1	Q2	Q3	Q4	A6*W	A8*W	A10*W	A15*W	A20*W	A25*W	A32*W	BW
M1000	0.007							0.09	0.09	0.09					0.1
M2000	0.02		0.1		0.04	0.09	0.13		0.16	0.16	0.16				0.15
M3000	0.02	0.1	0.1		0.04	0.09	0.13		0.16	0.16	0.16				0.17
M4000	0.02	0.1	0.1	0.024	0.05	0.10	0.14		0.16	0.16	0.16	0.16			0.21
M6000	0.02	0.1	0.1		0.05	0.10	0.14					0.53	0.53	0.53	0.34
M8000	0.02	0.1	0.1									0.53	0.53	0.53	0.36

Clean-room specifications (Catalog No. CB-033SA)

- Anti-dust generation structure for use in cleanrooms

M*000 - - **P7***

Specifications for rechargeable battery (Catalog No. CC-1226A)

- Design compatible with rechargeable battery manufacturing process

M*000 - - **P4***

F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain Separ
Mech Press SW
Res press exh valve
SlowStart
Anti-bac/Bac-remove Filt
Film Resist FR
Oil-Prohr
Med Press FR
No Cu/ PTFE FRL
Outdrs FRL
Adapter Joiner Press Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/ other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro Press SW
ContactSW
AirSens
PresSW Cool
Air Flo Sens/Ctrl
WaterRISens
TotAirSys (Total Air)
TotAirSys (Gamma)
Gas generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg etc
Ending

Oil Mist Filter Series

How to order

M1000 - **6** - **W** - **S** - **A6W** -

A Model No.

B Port size

C Port thread

D Option

E Display unit

F Pipe adaptor set (included)

G Bracket (included)

* Refer to page 30 for the explanation of the options.

A Model No.

Code	Description	M1000	M2000	M3000	M4000	M6000	M8000
B Port size							
6	1/8	●					
8 *1	1/4	●	●	●	●		
10	3/8		●	●	●		
15	1/2				●		
20	3/4					●	●
25	1					●	●

C Port thread		*2					
Blank	Rc thread	●	●	●	●	●	●
N	NPT thread	●	●	●	●	●	●
G	G thread	●	●	●	●	●	●

D Option		*3					
Drain *4*5 Discharge	Blank	With manual drain cock					
	F1	Auto-drain with man/override (NC: No press → no exhaust)					
Bowl Material	Blank	Polycarbonate bowl					
	Z	Nylon bowl					
	M	Metal bowl					
	M1	Metal bowl with manual drain cock					
Mantle (Element)	Blank	M type (nominal 0.01 μm; remaining oil 0.01 mg/m ³)					
	S	S type (0.3 μm; remaining oil 0.5 mg/m ³)					
	X *6	X type (deodorization; remaining oil 0.003 mg/m ³)					
	X *6	X type (deodorization; remaining oil 0.003 mg/m ³)					
Diff press Detect	Blank	Without differential pressure detection port					
	Q	With differential pressure detection port (Rc1/4)					
Differential pressure indicator	Blank	No differential pressure indicator					
	Q1 *7	With differential pressure indicator *8					
	Q2	With differential pressure indicator					
Diff press SW	Q3	Differential pressure indicator + switch 1-point (SW2)					
	Q4	Differential pressure indicator + switch 2-point (SW1/SW2)					
Flow Direction	Blank	Standard flow (left → right)					
	X1	Reverse flow (right → left)					

E Display unit							
Blank	MPa display (Rc thread), psi display (NPT thread), bar display (G thread)	●	●	●	●	●	●
J1	MPa display (NPT, G threads)	●	●	●	●	●	●

F Pipe adaptor set (included)		*8 *9 page 350					
Blank	Not included	●	●	●	●	●	●
A6*W	1/8 pipe adaptor set	●					
A8*W	1/4 pipe adaptor set	●	●	●	●		
A10*W	3/8 pipe adaptor set	●	●	●	●		
A15*W	1/2 pipe adaptor set		●	●	●		
A20*W	3/4 pipe adaptor set				●	●	●
A25*W	1 pipe adaptor set					●	●
A32*W	1 1/4 pipe adaptor set					●	●

* Adaptor thread							
Blank	Rc thread	●	●	●	●	●	●
N	NPT thread	●	●	●	●	●	●
G	G thread	●	●	●	●	●	●

G Bracket (included)		Page 346					
Blank	Not included	●	●	●	●	●	●
BW	C-bracket	●	●	●	●	●	●

⚠ Precautions for model No. selection

*1: "Q1" with differential pressure indicator and "Q3" "Q4" differential pressure switch cannot be selected for port size "8".

*2: G threads and NPT threads are available for IN, OUT and drain outlet (metal bowl with auto-drain).

*3: Select options for drainage, bowl material and differential pressure detection. When selecting options for several items, list options in order from the top.

*4: NO auto-drain cannot be selected.

*5: Refer to page 354 for the auto-drain usage conditions.


*6: "X" mantle cannot be combined with F1 option or "Q1" (with differential pressure indicator).

*7: "Q1" with differential pressure indicator cannot be selected for bowl material "M".

*8: The pipe adaptor set and C type bracket cannot be used together.

*9: The joiner set is included with the pipe adaptor set.

Ⓛ Options: Differential pressure indicator/differential pressure switch




Oil Mist Filter series


Flow characteristics (max. processing flow rate)

Flow characteristics (max. processing flow rate)


● M*000-W-M



● M*000-W-S




● M*000-W-X



● M1000-W-F1

With auto-drain (M type, S type)



How to select oil mist filter and optional mantle

Recommended circuit

◆ S type



- Applications
General industrial air
- Air tool
 - Air drill/air screw driver
 - Pneumatic grinder
 - Labor-saving device
 - Pneumatic jigs and tools
 - Air chuck
 - Air vice
 - Precision part cleaning air blow

◆ M type






- Oil-free air
- Instrumentation
 - Measurement
 - For sequence control
 - Movable element/pure fluid element
 - Luxury painting
 - Precision industry

◆ X type



- Odorless air
- Food industry
 - Pharmaceutical industry
 - Mixing
 - Transportation
 - Drying
 - Packaging
 - Brewing air

Option code of mantle and shape

Option code	Appearance
Blank (M type)	
S (S type)	
X (X type)	

Note: Changes for product upgrades may be made without prior notice.
When placing an order, confirm the option code of the part model No. displayed on the body.


F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain Separ
Mech Press SW
Res press exh valve
SlowStart
Anti-bac/Bac-remove Filt
Film Resist FR
Oil-ProhR
Med Press FR
No Cu/ PTFE FRL
Outdrs FRL
Adapter Joiner Press Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/ other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro Press SW
ContactSW
AirSens
PresSW Cool
Air Flo Sens/Ctrl
WaterRISens
TotAirSys (Total Air)
TotAirSys (Gamma)
Gas generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg etc
Ending

Oil Mist Filter Series


F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain
Separ
Mech
Press SW
Res press
exh valve
SlowStart
Anti-bac/Bac-
remove Filt
Film
Resist FR
Oil-ProhR
Med
Press FR
No Cu/
PTFE FRL
Outdrs FRL
Adapter
Joiner
Press
Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/
other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro
Press SW
ContactSW
AirSens
PresSW
Cool
Air Flo
Sens/Ctrl
WaterRtSens
TotAirSys
(Total Air)
TotAirSys
(Gamma)
Gas
generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg
etc
Ending

Internal structure and parts list


● M1000-W




● M2000-W




● M3000-W/M4000-W



● M6000-W



● M8000-W




No.	Part name	Material					
		M1000-W	M2000-W	M3000-W	M4000-W	M6000-W	M8000-W
1	Plate cover	ABS resin					
2	Body	Polyamide resin	Aluminum alloy die-casting				
3	O-ring *1	Special nitrile rubber					
4	Mantle assembly	-					
5	Bowl assembly	Polycarbonate resin, polyacetal resin, urethane resin					
6	Bowl guard	Polyamide resin	Polyamide resin, steel				

*1: The O-ring of the M1000-W has a special shape.


Dimensions



● M1000-W



● M2000-W



F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain Separ
Mech Press SW
Res press exh valve
SlowStart
Anti-bac/Bac-remove Filt
Film Resist FR
Oil-ProhR
Med Press FR
No Cu/ PTFE FRL
Outdrs FRL
Adapter Joiner Press Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/ other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro Press SW
ContactSW
AirSens
PresSW Cool
Air Flo Sens/Ctrl
WaterRISens
TotAirSys (Total Air)
TotAirSys (Gamma)
Gas generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg etc
Ending


Oil Mist Filter Series




F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain
Separ
Mech
Press SW
Res press
exh valve
SlowStart
Anti-bac/Bac-
remove Filtr
Film
Resist FR
Oil-ProhR
Med
Press FR
No Cu/
PTFE FRL
Outdrs FRL
Adapter
Joiner
Press
Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/
other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro
Press SW
ContactSW
AirSens
PresSW
Cool
Air Flo
Sens/Ctrl
WaterRtSens
TotAirSys
(Total Air)
TotAirSys
(Gamma)
Gas
generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg
etc
Ending

Dimensions

● M3000-W




- Attachment
C type bracket (-BW)
Part model No.: B320
- Material: Steel
Zinc plated




- For the plastic bowl, the dimensions of the manual cock and the auto-drain are the same.
Note: The C type bracket and pipe adaptor set attachments cannot be used together.



● M4000-W



- Attachment
C type bracket (-BW)
Part model No.: B420
- Material: Steel
Zinc plated



- Dimensions of options
With differential pressure
indicator (Q1)




- (Note): Normally green, and red
when replacing the element

Dimensions




● M6000-W



● For the plastic bowl, the dimensions of the manual cock and the auto-drain are the same.
Note: The C type bracket and pipe adaptor set attachments cannot be used together.


● M8000-W



● For the plastic bowl, the dimensions of the manual cock and the auto-drain are the same.


- Attachment
C type bracket (-BW)
Part model No.: B620
- Material: Steel

Zinc plated



- Attachment
C type bracket (-BW) Part
model No.: B820
- Material: Steel

Zinc plated




F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain Separ
Mech Press SW
Res press exh valve
SlowStart
Anti-bac/Bac-remove Filt
Film Resist FR
Oil-ProhR
Med Press FR
No Cu/ PTFE FRL
Outdrs FRL
Adapter Joiner Press Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/ other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro Press SW
ContactSW
AirSens
PresSW Cool
Air Flo Sens/Ctrl
WaterRISens
TotAirSys (Total Air)
TotAirSys (Gamma)
Gas generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg etc
Ending

Oil Mist Filter Series




Optional dimensions

- Metal bowl (option)
[M2000-W, M3000-W, M4000-W, M6000-W, M8000-W]



- With differential pressure indicator, differential pressure switch (options)
(M2000-W, M3000-W, M4000-W, M6000-W)



- The dimensions of the manual cock and the auto-drain are the same.
Note: The C type bracket and piping adapter set attachments cannot be used together.


Code	Port size	A	B	C	D	E	F
M2000-W	Rc1/4(8), Rc3/8(10)	50	62	22.5	147	50	(28)
M3000-W	Rc1/4(8), Rc3/8(10)	63	62	22.5	148	63	(34.5)
M4000-W	Rc3/8(10), Rc1/2(15)	80	62	22.5	171	79	(42.5)
M6000-W	Rc3/4(20), Rc1(25)	90	72.5	33	210	85	42.5

Dimensions table

Model No.	F1M	M	M1
	A	B	C
M2000-W	-	-	147
M3000-W	164	143.5	154
M4000-W	187	166.5	177
M6000-W	226	205	216
M8000-W	319	298	309

- Material of the metal bowl is aluminum die-casting.

Optional parts list - for oil mist filters



Repair parts kit model No. (set including O-ring, mantle and bowl O-ring)

Model	M type	S type	X type
M1000-W	M1000-KIT	M1000-KIT-S	M1000-KIT-X
M1000-W-F1	M1000-KIT-F1	M1000-KIT-F1S	-
M2000-W	M2000-KIT	M2000-KIT-S	M2000-KIT-X
M3000-W,MM3000-W	M3000-KIT	M3000-KIT-S	M3000-KIT-X
M4000-W,MM4000-W	M4000-KIT	M4000-KIT-S	M4000-KIT-X
M6000-W,MM6000-W	M6000-KIT	M6000-KIT-S	M6000-KIT-X
M8000-W,MM8000-W	M8000-KIT	M8000-KIT-S	M8000-KIT-X

Repair parts kit model No. (set including O-ring and mantle)

Model	M type	S type	X type
M1000-W	M1000-MANTLE-ASSY	M1000-MANTLE-ASSY-S	M1000-MANTLE-ASSY-X
M1000-W-F1	M1000-MANTLE-ASSY-F1	M1000-MANTLE-ASSY-F1S	-
M2000-W	M2000-MANTLE-ASSY	M2000-MANTLE-ASSY-S	M2000-MANTLE-ASSY-X
M3000-W,MM3000-W	M3000-MANTLE-ASSY	M3000-MANTLE-ASSY-S	M3000-MANTLE-ASSY-X
M4000-W,MM4000-W	M4000-MANTLE-ASSY	M4000-MANTLE-ASSY-S	M4000-MANTLE-ASSY-X
M6000-W,MM6000-W	M6000-MANTLE-ASSY	M6000-MANTLE-ASSY-S	M6000-MANTLE-ASSY-X
M8000-W,MM8000-W	M8000-MANTLE-ASSY	M8000-MANTLE-ASSY-S	M8000-MANTLE-ASSY-X

* M parts should be selected as they are compatible with M1000-W, 3000-W, 4000-W, and 8000-W Series products released before May 1998.

* Refer to the air filter options and parts table for details on the bowl assembly and bowl guard.

F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain Separ
Mech Press SW
Res press exh valve
SlowStart
Anti-bac/Bac-remove Filtr
Film Resist FR
Oil-ProhR
Med Press FR
No Cu/ PTFE FRL
Outdris FRL
Adapter Joiner Press Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/ other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro Press SW
ContactSW
AirSens
PresSW Cool
Air Flo Sens/Ctrl
WaterRISens
TotAirSys (Total Air)
TotAirSys (Gamma)
Gas generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg etc
Ending