

Separated

F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain
Separ
Mech
Press SW
Res press
exh valve
SlowStart
Anti-bac/Bac-
remove Filtr
Film
Resist FR
Oil-Prohr
Med
Press FR
No Cu/
PTFE FRL
Outdrs FRL
Adapter
Joiner
Press
Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneur
AirBoost
Speed Ctrl
Silncr
CheckV/
other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro
Press SW
ContactSW
AirSens
PresSW
Cool
Air Flo
Sens/Ctrl
WaterRtSens
TotAirSys
(Total Air)
TotAirSys
(Gamma)
Gas
generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg
etc
Ending

For air filter

Many options are available for the CKD air filter.
When selecting the model No. of the air filter, carefully consider the environment in which the air filter is to be used.

If an option is required, order with an option code added at the end of the model No.
(Example) If a metal bowl is installed onto the 1138-6C, 1138-6C-M shall be specified.

Bowl options table

Compatible model No.		1138 1126 1226 1226J	1238
Compatible model		1138	1238
Option code	Blank	○	○
	E	○	○
	F	○ *1	
	F1	○	○
	Z	○	
	EZ	○	
	FZ	○ *1	
	F1Z	○	
	M	○	○
	FM	○ *1	
	F1M	○	○
	MG	○	○
	FMG	○ *1	
	F1MG	○	○

How to order bowl assembly

(A set of bowl assembly and O-ring for sealing)

1138 – BOWL – FM

A Model No.	B Option code			
	Drain discharge		Bowl material	
1138	Blank	Manual drain cock	Blank	Polycarbonate resin
1238	E	Flexible drain	Z	Transparent nylon resin
	F	NO auto-drain with manual cock (exhaust when not pressurized)	M	Metal bowl
	F1	NC auto-drain with manual cock (no exhaust when not pressurized)	MG	Metal bowl with side gauge


Select in order of the drainage, size and bowl material.

*1: Do not apply F (NO auto-drain) to micro alescra.

*2: Refer to page 480 for the auto-drain usage conditions

Other bowl assembly model No. table

Bowl material	Compatible model No.	
	1326/5100	A1338
Polycarbonate resin	5100-BOWL	A1338-BOWL
Nylon resin	5100-BOWL-Z	—
Metal bowl	5100-BOWL-M	A1338-BOWL-M
Metal bowl with side gauge	5100-BOWL-MG	A1338-BOWL-MG



Air filter with 3 μ m element

Max. flow rate table Atmospheric pressure conversion value for primary pressure 0.7 MPa and pressure drop 0.034 MPa

Model No.	Port size	Max. flow rate (l/min ANR)
1138-6C-EX	Rc ³ / ₄	4,800
1138-8C-EX	Rc1	6,400
1126-10C-EX	Rc1 ¹ / ₄	13,000
1126-12C-EX	Rc1 ¹ / ₂	13,000
1126-16C-EX	Rc2	13,000

F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain Separ
Mech Press SW
Res press exh valve
SlowStart
Anti-bac/Bac-remove Filt
Film Resist FR
Oil-ProhR
Med Press FR
No Cu/ PTFE FRL
Outdrs FRL
Adapter Joiner Press Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/ other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro Press SW
ContactSW
AirSens
PresSW Cool
Air Flo Sens/Ctrl
WaterRISens
TotAirSys (Total Air)
TotAirSys (Gamma)
Gas generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg etc
Ending


Separated

F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain Separ
Mech Press SW
Res press exh valve
SlowStart
Anti-bac/Bac- remove Filt
Film Resist FR
Oil-ProhR
Med Press FR
No Cu/ PTFE FRL
Outdrs FRL
Adapter Joiner
Press Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/ other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro Press SW
ContactSW
AirSens
PresSW Cool
Air Flo Sens/Ctrl
WaterRtSens
TotAirSys (Total Air)
TotAirSys (Gamma)
Gas generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg etc
Ending

Regulator

Many options are available for CKD regulator.
When selecting the regulator model No., select the product according to the working conditions of the regulator.

If an option is required, order with an option code added at the end of the model No.
(Example) If a plastic knob is installed onto the 2215-8C, 2215-8C-K shall be specified.



Specifications

Model	Model No.	Pressure adjusting range
Regulator for high pressure	2215-6/8/10C-H	0.07 to 1.23 MPa


Attached pressure gauge

Model		Attached pressure gauge	
		G	LG
2215	2216	G59D-8-P10	G59D-8-P04
2415	2302		
2303	2304		
2215-H		G59D-8-P20	
2216-H			

For lubricator

Many options are available for CKD lubricator. When selecting the model No. of lubricator, carefully consider the type of lubricant and working environment.

If an option is required, order with an option code added at the end of the model No. (Example) If a metal bowl is installed onto the 3003E-6C, 3003E-6C-M shall be specified.



Bowl assembly and model No. table (set of bowl assembly and O-ring for sealing)

Compatible model	Polycarbonate resin bowl			Transparent nylon resin bowl			Metal bowl		
	Blank	Manual cock	Auto-fill	Blank	Manual cock	Auto-fill	Blank	Manual cock	Auto-fill
A3019	A3019-BOWL	A1019-BOWL	—	A3019-BOWL-Z	A1019-BOWL-Z	—	—	A1019-BOWL-M	—
3003E/3503E	3003E-BOWL	1138-BOWL	3003E-BOWL-V	3003E-BOWL-Z	1138-BOWL-Z	3003E-BOWL-VZ	3003E-BOWL-M	1138-BOWL-M	3003E-BOWL-VM
Compatible model	Metal bowl with side gauge								
	Blank	Manual cock	Auto-fill	2l	8l	20l			
A3019	—	—	—	—	—	—			
3003E/3503E	3003E-BOWL-MG	1138-BOWL-MG	3003E-BOWL-VMG	3003E-BOWL-MG2	3003E-BOWL-MG8	3003E-BOWL-MG20			
				3004E-BOWL-MG2	3004E-BOWL-MG8	3004E-BOWL-MG20			
				3005E-BOWL-MG2	3005E-BOWL-MG8	3005E-BOWL-MG20			
				3005E-BOWL-MG2	3005E-BOWL-MG8	3005E-BOWL-MG20			

*1: The quart bowl number for 2 l to 20 l contains an adaptor, screws, a gasket and a siphon tube assembly, etc., for installation.

*2: Quart bowl for 2 l to 20 l is a made-to-order product.

*3: Indicate "blank" for a bowl without cock. Blanking plug assembly applies to a metal bowl without cock "M".

*4: Siphon tube assembly is attached for MG2/MG8/MG20.

F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain Separ
Mech Press SW
Res press exh valve
SlowStart
Anti-bac/Bac-remove Filtr
Film Resist FR
Oil-ProhR
Med Press FR
No Cu/ PTFE FRL
Outdrs FRL
Adapter Joiner Press Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/ other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro Press SW
ContactSW
AirSens
PresSW Cool
Air Flo Sens/Ctrl
WaterRiSens
TotAirSys (Total Air)
TotAirSys (Gamma)
Gas generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg etc
Ending