



Air tank (related products)

AT Series

JIS symbol



Features


Air tank directly connected to air booster ABP-12 with compact body.

Specifications

Item	AT
Working fluid	Compressed air
Max. working pressure MPa	0.99 (≈140 psi, 9.9 bar)
Water pressure test pressure MPa	1.5 (≈220 psi, 15 bar)
Ambient temperature °C	0 (32°F) to 50 (122°F) (no freezing)
Internal capacity m ³	0.024
Port size	Rc1/2
Material	Steel
Weight kg	17.5

Note: O-ring, hexagon head bolt and spring washer are included for air booster mounting.

How to order



● Part model No.

AT-K1 (O-ring, hex head bolt, spring washer)

Dimensions

