



Manual air dryer (desiccant)

4001/4002 Series

Stable supply of ultra dry air with atmospheric dew point -72°C.

- Processing air flow rate: 280 ℓ/min (ANR) or less



Specifications


Item	4001-2C		4002-2C
Max. working pressure MPa	1.0 *1		
Proof pressure MPa	1.5 (≈220 psi, 15 bar)		
Inlet air temperature range °C	5 (41°F) to 32 (89.6°F)		
Ambient temperature °C	5 (41°F) to 65 (149°F)		
Atmospheric dew point °C	-43 (-45.4°F)		
Max. flow rate ℓ/min(ANR)	280 (at 0.7 MPa (≈100 psi, 7 bar)) *2, *3		
Desiccant	Silica gel		
Port size Rc	1/4		1/4
Weight kg	4.6		10

*1: The working pressure of 4002-2C is 0.2 MPa to 1.0 MPa.


*2: The max. flow rate at 0.7 MPa inlet air pressure calculated with the atmospheric pressure conversion value.

*3: The min. flow rate required for 4002-2C is 30 ℓ/min (ANR).

How to order



Functions



- (1) Clamp ring
Push-in clamp ring for easy replacement of desiccant.
- (2) Desiccant
Silica gel (atmospheric dew point: -43°C) and other molecular sieves (atmospheric dew point: -72°C) are provided as desiccant. Very small holes of these desiccants trap moisture from the passing compressed air, which is known as capillary action, and thus dry the compressed air.
- (3) Screen
Desiccant prevents scattering due to air flow.


Performance list

Model No.	Atmospheric dew point	Max. inlet air temperature	Max. flow rate	Desiccant	Desiccant No.	Remarks
4001-2C 4002-2C	-43°C	32°C	280 ℓ/min(ANR)	Silica gel	4001-SILICA-GEL	Non-regenerable
4001-2C-U 4002-2C-U	-72°C	32°C	280 ℓ/min(ANR)	4AM.S.	85-060	Non-regenerable
4001-2C-X 4002-2C-X	Oil removal 24 PPM _W	32°C	280 ℓ/min(ANR)	13XM.S.	85-061	Non-regenerable


Note: M.S. means molecular sieves.

Dimensions

● 4001-2C



● 4002-2C



⚠ Safety precautions

- Fill the bowl with desiccant up to just below the screen (approximately 0.8 kg). Be careful not to allow any desiccant to enter the tube.
- Keep the max. flow rate below 280 l/min. Replace the desiccant (silica gel) if it has changed from green to orange. The desiccant adsorbs approx. 100 g of moisture. (Desiccant weight 0.8 kg included)
- Use 4001-2C-U if the atmospheric dew point of -72°C is required. As the color does not change even when moisture is adsorbed, attach a moisture indicator (6119-2C) after 4001-2C-U or 4002-2C-U. Desiccant service life can be checked.
- To remove oil of the compressed air, use 4001-2C-X or 4002-2C-X. The color will change from yellowish brown to blackish brown when oil is adsorbed. Replace it when the color has changed. 113 g of oil content is adsorbed before replacement.
- Avoid direct sunlight.
- Installing an air filter is recommended to obtain cleaner air.
- Carefully prevent water drops from entering the inside. Otherwise heat generation may occur.

F.R.L.
F.R.
F (Filtr)
R (Reg)
L (Lub)
Drain Separ
Mech Press SW
Res press exh valve
SlowStart
Anti-bac/Bac-remove Filtr
Film Resist FR
Oil-ProhR
Med Press FR
No Cu/ PTFE FRL
Outdrs FRL
Adapter Joiner Press Gauge
CompFRL
LgFRL
PrecsR
VacF/R
Clean FR
ElecPneuR
AirBoost
Speed Ctrl
Silncr
CheckV/ other
Fit/Tube
Nozzle
Air Unit
PrecsCompn
Electro Press SW
ContactSW
AirSens
PresSW Cool
Air Flo Sens/Ctrl
WaterRISens
TotAirSys (Total Air)
TotAirSys (Gamma)
Gas generator
RefrDry
DesicDry
HiPolymDry
MainFiltr
Dischrg etc
Ending